

# Mosaic™ mechanisms

## dimming control



0 792 07A



0 784 04



0 784 10



Selection chart for boxes, supports and plates **p. 1198-1199**

Pack	Cat.Nos	Push-dimmer without neutral, 2 wires
		<p>Can be associated with one or several push-buttons (non illuminated type). Each push-button able to perform the On/Off and dimming function</p> <p>When switched on, lights up at the level set before last switch-off</p> <p>Standby consumption &lt; 5 mW</p> <p>For all types of lamps:</p> <ul style="list-style-type: none"> <li>- Dimmable LEDs and CFLs: 3 to 125 W LED (10 lamps max.)</li> <li>- Halogen, incandescent 230 V~ : 3 to 125 W</li> <li>- Halogen with ferromagnetic or electronic transformer: 3 to 125 VA (specific setting mode for this load charge)</li> <li>- ELV Halogen with ferromagnetic or electronic transformer: 3 to 125 VA (specific setting mode for this load charge)</li> </ul> <p>2 modules</p> <p><b>Mechanism</b></p> <p>To be equipped with support and plate</p> <p> <input type="radio"/> White  <input type="radio"/> Alu  <input type="radio"/> Matt Black         </p> <p><b>Supplied complete</b></p> <p>Supplied with support and plate</p> <p> <input type="radio"/> White         </p>
1	0 784 07A	
1	0 792 07A	
1	0 791 07LA	
1	0 488 70LA	

Pack	Cat.Nos	Push-dimmer with neutral, 3 wires
		<p>Can be associated with one or several push-buttons (non illuminated type). Each push-button able to perform the On/Off and dimming function</p> <p>When switched on, lights up at the level set before last switch-off</p> <p>Standby consumption &lt; 5 mW</p> <p>For all types of lamps:</p> <p>Dimmable LEDs and CFLs: 0 to 150 W LED (15 lamps max.)</p> <p>Halogen, incandescent 230 V~ : 0 to 150 W</p> <p>Halogen with ferromagnetic or electronic transformer: 0 to 150 VA (specific setting mode for this load charge)</p> <p>ELV Halogen with ferromagnetic or electronic transformer: 0 to 150 VA (specific setting mode for this load charge)</p> <p>2 modules</p> <p> <input type="radio"/> White  <input type="radio"/> Alu  <input type="radio"/> Matt Black         </p>
1	0 784 08A	
1	0 792 08A	
1	0 791 08LA	

Pack	Cat.Nos	Dimmer switch with neutral, for 0-10 V ballast
		<p>Incorporates the dimming level memory function: the light comes on at the lighting level set prior to the last switch-off</p> <p>Can be combined with one or more non-illuminated push-buttons, with each push-button then providing the on/off and dimming functions</p> <p>For lamps with 0-10 V ballast, 600 VA</p> <p>2 modules</p> <p> <input type="radio"/> White         </p>
1	0 784 04	
1	0 401 49	<p><b>Active Power Bleeder</b></p> <p>Allows 2-wire electronic switches without neutral to be compatible with all loads (LED, fluocompact...)</p> <p>Consumption : 1.8 W (0.2 W on stand-by)</p>
1	0 784 10	<p><b>Auxiliary control unit for DIN dimmer</b></p> <p>Remote control dimming peripheral for local control of a remote control dimmer, with the same easy operation as a conventional dimmer</p> <p>A power supply Cat.No 0 036 80 is required for controlling DIN-rail modular remote control dimmers Cat.Nos 0 036 60/71</p> <p>2 modules</p>