


distribution blocks

self assembly




Insulated supports (maximum 280 A)

Pack	Cat. Nos.	Description	Mounting type
5	0373 96	For assembling distribution blocks of varying lengths using bars and connectors below. Supplied with insulated screws for mounting optional protective cover (except Cat. No. 0373 98). Set of 2 insulated 4 pole supports For bars 12 x 2 or 12 x 4 mm	DIN rail 0044 16 supplied or M4 screws not supplied
10	0373 98	Single pole supports For bars 12 x 2 or 12 x 4 mm	by M4 screws supplied
10	0374 37	For bars 15 x 4, 18 x 4 or 25 x 4 mm	

Copper connector bars

With threaded holes


		Size (mm)	Threaded holes Ø mm	Pitch	Max. thermal rating (A)	Length (mm)
10	0373 88	12 x 2	M5	18	110	990
10	0373 89	12 x 4	M5	18	160	990
10	0374 33	15 x 4	M6	18	200	990
10	0374 34	18 x 4	M6	18	245	990
10	0374 38	25 x 4	M6	18	280	990
4	0374 19	32 x 5	M6	25	450	1750



Connectors


Clamp type – For bars with threaded holes 12 x 4 (mm)

100	0373 65	For one or two conductors 1.5 to 10 mm ² (supplied with Ø 5 mm screw)
-----	---------	--




Clips

10	0044 16	For mounting on rail EN 60715 and 15 mm depth 10 mm width With threaded Ø 4 mm hole
----	---------	---




Copper connector bars with threaded holes


Cat. Nos. 0373 88/89




Cat. Nos. 0374 33/34



Cat. No. 0374 38



Cat. No. 0374 19



Cat. Nos.	Size	lth (A)	lc (A)
0373 88	12 x 2	110	80
0373 89	12 x 4	160	125
0374 33	15 x 4	200	160
0374 34	18 x 4	245	200
0374 38	25 x 4	280	250
0374 19	32 x 5	450	400

Current ratings according to EN 60947-1 :


- lth : bars in free air
- lthe : bars enclosed with ventilation
- lc : bars totally enclosed in a weatherproof enclosure

Insulated supports four pole

Insulation voltage according to EN 60947-1/IEC 60664-1 :
Cat. No. 0373 96 : 690 V - Impulse voltage (surge) (Uimp) : 8 kV
Degree of pollution (conductive dust) : 3
Distance between supports (mm)

Cat. Nos.	0373 96
Bar size	12 x 4 (12 x 2)
In (A)	125 (80)
Peak withstand current (kA)	
10	400 (200)
15	300 (150)
20	200 (125)
25	150 (100)
30	-
35	-
40	-

Cat. No. 0373 96




Insulated supports single pole


Insulation voltage according to EN 60947-1/IEC 60664-1 : 500 V
Impulse voltage (surge) (Uimp) : 8 kV
Degree of pollution (conductive dust) : 3

Cat. No. 0373 98


Front view for 12 x 2 mm bar




View from above



Front view for 12 x 4 mm bar



Cat. No. 0374 37



Max. space between 2 supports :
bar size 12 x 2 : 20 cm, 12 x 4 : 25 cm

The distance between supports can be determined using the chart
Select the peak withstand current (kA rating) and the distance between bars - dimension E (mm) after choosing your bar and support
Distance between supports (mm)

Cat. Nos.	0373 98				0374 37			
	12 x 2/12 x 4				15 x 4/18 x 4/25 x 4			
In (A)	80/125				160/200/245			
E (mm)	50	75	100	125	50	75	100	125
Peak withstand current (kA)								
10	400	600	800	-	350	600	750	-
15	300	450	600	800	250	400	500	700
20	250	350	450	600	150	225	300	375
25	200	250	300	400	125	150	200	250
30	-	-	-	-	100	125	150	175
35	-	-	-	-	-	100	125	150