

Mosaic™ mechanisms

voltage surge protector, replacement module, buzzers, bells, blanking plates and cable outlets



Selection chart for boxes, supports and plates p. 1198-1199

Pack	Cat.Nos	
		Voltage surge protector
1	0 775 40	<p>16 A - 250 V\sim - 50/60 Hz Protection against overvoltages of atmospheric or industrial origin, in an installation already protected by a voltage surge protector in the panel For installation downstream of an RCBO, protects all the sockets wired in cascade with the voltage surge protector. Operation displayed by indicator light Keeps the socket energised after an overvoltage (mains or lightning strike) until replacement of module Cat.No 0 775 41 Nominal discharge current (In): 1,5 kA Maximum permissible current (Imax): 6 kA Protection level (Up): L-N: 1 kV; N-PE: 1 kV Open circuit voltage (Uoc): 3 kV Conform to standards EN 61643-11</p> <p> White 2 modules</p>
1	0 775 41	<p>Replacement module for voltage surge protector</p> <p> For Cat.No 0 775 40</p>
		Buzzers and bells
10	0 766 40	<p>Buzzers - 2 modules</p> <p> White - 8 V\sim - 50/60 Hz Consumption 370 mA Sound level 70 dB at 1 m</p>
10	0 766 41	<p> White - 230 V\sim - 50/60 Hz Consumption 25 mA Sound level 70 dB at 1 m</p>
1	0 766 42	<p>Electronic bell - 2 modules</p> <p> White 12-24-48 V\approx Consumption 5-9-17 mA Sound level 80 dB at 1 m</p>
		Blanking plates
		For Mosaic mechanisms
10	0 770 70	<p>1 module</p> <p> <input type="radio"/> White <input type="radio"/> Alu <input type="radio"/> White antimicrobial⁽¹⁾ <input type="radio"/> Matt Black</p>
10	0 792 70	
10	0 787 20	
10	0 793 70L	
10	2 770 71L	<p>2 modules</p> <p> <input type="radio"/> White <input type="radio"/> Alu <input type="radio"/> Matt Black <input type="radio"/> White antimicrobial⁽¹⁾</p>
10	0 792 80	
10	0 791 81L	
10	0 787 21	
		Tap-off
10	0 775 53	<p>Equipped with 3 terminals to facilitate the 20 A tap-off</p> <p> 2 modules <input type="radio"/> White</p>
		Cable outlets
10	0 775 51	<p>16 A with cable grip - 2 modules</p> <p>Equipped with 4 automatic connection terminals on the front and rear faces for easy connection</p> <p> <input type="radio"/> White</p>
10	2 775 50L	<p>20 A with cable grip - 2 modules</p> <p><input type="radio"/> White <input type="radio"/> White (pack of 50) <input type="radio"/> Alu <input type="radio"/> Matt Black</p>
10	0 775 59	
10	0 792 49	
10	0 791 50L	
10	0 775 52	<p>Ø8 mm wire outlet - 1 module</p> <p> <input type="radio"/> White</p>
1	0 770 80	<p>Anti-extraction module</p> <p>When used with a socket, avoids accidental unplugging of sensitive electrical equipment, by gripping the cord (Ø4 to 8 mm cords) Can withstand an extraction force of 350 N (35 kgs) 1 module - white antimicrobial⁽¹⁾</p> <p></p>

1: Contains a silver compound to prevent the growth of bacteria on the surface of the plate