



Viking 3 accessories for terminal blocks (continued)




0372 81 (p. 57) + 0375 24



0371 63/0371 03 (p. 52) + 0375 66



0371 61 (p. 52) + 0375 27



Shielding terminal block with end stops Cat. No. 0375 12 (p. 58), shielding bar Cat. No. 0375 34 and clamps Cat. Nos. 0375 30/31

Technical characteristics p. 63

Pack	Cat. Nos.	Bridging accessories (continued)
		Bars for screw terminal blocks Front mounting with screws. Pre-assembled Consecutive or alternating connection
10	0375 40	For 12 blocks with 10 mm width
10	0375 42 ¹	For 12 blocks with 12 mm width
10	0375 44	For 12 blocks with 15 mm width
		Bridging combs for 3-level screw terminal blocks For lower and intermediate levels of blocks Cat. Nos. 0371 51/52 (p. 121). Side mounting Isolated and separable
10	0375 46	Brown. For 12 blocks with 5 mm width
10	0375 47	Blue. For 12 blocks with 5 mm width
		Bridging combs for spring terminal blocks Front mounting (automatic insertion), screwless Isolated. Red
20	0375 82	For 2 blocks with 10 mm width
20	0375 85	For 2 blocks with 12 mm width
		Accessories for disconnection blocks For screw and spring terminal blocks
		Blown fuse indicators Clip directly on to blocks Cat. Nos. 0371 81 (p. 52) or 0372 81 (p. 53)
50	0375 24	12/24/48 V _~ / \sim for block with fuse cartridge 5 x 20 with handle lever
50	0375 25	110/250 V _~ for block with fuse cartridge 5 x 20 with handle lever

Pack	Cat. Nos.	Shielding accessories
		Ensure safe, simple connection of cable shielding
		Shielding clamps For screw and spring terminal blocks - mounted by pivoting on collector bar 10 x 3 mm Cat. No. 0375 34 - mounted on plate with M4 screws (supplied) - mounted on rail with Cat. No. 0364 69 (p. 58)
10	0375 30	For cable diameter 3 to 8 mm
10	0375 31	For cable diameter 4 to 13.5 mm
4	0375 32	For cable diameter 10 to 20 mm
		Shielding bar For screw and spring terminal blocks. Steel. Length 1 m For use with end stop Cat. No. 0375 12 (p. 58) 10 x 3 mm
10	0375 34	
50	0375 35	Screening continuity bracket For screw terminal blocks 1 entry/1 exit 5, 6, 8 and 10 mm width Connected with 2.8 x 0.8 mm clips or welded on. Capacity : 1 mm ²
		Protective screens
		1 pole For screw terminal blocks 1 entry/1 exit
10	0375 65	5 and 6 mm width
10	0375 66	8 and 10 mm width
10	0375 67	12 and 15 mm width
		Cut to length Length 1 m Mounted on separation and insulation divider For screw terminal blocks 1 entry/1 exit
10	0375 68	5, 6, 8 and 10 mm width (divider Cat. No. 0375 60, p. 58)
10	0375 69	12 and 15 mm width (divider Cat. No. 0375 61, p. 58)
		Test meter adaptor
10	0375 27 ²	For screw and spring terminal blocks Measurement socket for \varnothing 4 mm plug for blocks with 5 and 6 mm width

1 : Except for Cat. No. 0371 87 (p. 53)

2 : Except for disconnection blocks with handle lever, screw terminal block with LED and spring function blocks. 2 and 3-level terminal blocks : upper level only