

# Hypra® IP 66/67-55 - LV 16 A

## plastic plugs and sockets



Technical information and dimensions **p. 99-101**  
 Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2, IEC 60309-1 and IEC 60309-2  
 IP according to BS EN 60529 and IEC 60529  
 IK 09  
 Self-extinguishing : 850 °C for insulated parts, 650 °C for housing  
 Stainless steel external screws - Nickel plated brass contacts  
 Temp. rating : -50 °C to +100 °C

Pack	Cat. Nos.		<b>Panel mounting sockets 16 A</b>
1	Plastic	Modular	Plastic version can be used with back boxes to create surface mounting sockets (modular version is not compatible with back boxes)
	0511 25		
5   1	0511 26	0511 46	<b>100 to 130 V~</b> 2 P + ⊥ <b>200 to 250 V~</b> 2 P + ⊥ <b>380 to 415 V~</b> 2 P + ⊥
1	0511 30	0511 50	<b>100 to 130 V~</b> 3 P + ⊥
1	0511 31	0511 51	<b>200 to 250 V~</b> 3 P + N + ⊥

Pack	Cat. Nos.	<b>Mobile sockets 16 A</b>
1	0511 75	<b>100 to 130 V~</b> 2 P + ⊥
1	0511 76	<b>200 to 250 V~</b> 2 P + ⊥
1	0511 80	<b>380 to 415 V~</b> 3 P + ⊥
1	0511 81	<b>380 to 415 V~</b> 3 P + N + ⊥

Pack	Cat. Nos.	<b>Straight plugs 16 A</b>
1	0511 55	<b>100 to 130 V~</b> 2 P + ⊥
1	0511 56	<b>200 to 250 V~</b> 2 P + ⊥
5	0511 60	<b>380 to 415 V~</b> 3 P + ⊥
5	0511 61	<b>380 to 415 V~</b> 3 P + N + ⊥

Pack	Cat. Nos.	<b>Angled plugs 16 A</b>
1	0511 06	<b>200 to 250 V~</b> 2 P + ⊥
1	0511 10	<b>380 to 415 V~</b> 3 P + ⊥
1	0511 11	<b>380 to 415 V~</b> 3 P + N + ⊥

Pack	Cat. Nos.	<b>Back boxes</b>
<b>Surface mounting boxes</b>		
5	0520 29	For LV 16 A 2 P + ⊥ sockets
5	0522 29	For LV 16 A 3 P + ⊥ / 3 P + N + ⊥ sockets
<b>Through entry surface mounting boxes</b>		
1	0520 89	For LV 16 A 2 P + ⊥ sockets
5	0522 89	For LV 16 A 3 P + ⊥ / 3 P + N + ⊥ sockets