








cavity floor service outlet boxes



 Cavity floor outlet boxes selection chart **p. 24-25**
 Dimensions and technical information **p. 28**
 Installation details **p. 29**

Pack	Cat. Nos.	Cavity floor boxes
1	CB3	Contractor floor box Supplied empty Ready to accept standard BS two gang wiring accessories Additional mounting plates not required Recommended hole cut-out size : 302-304 mm x 219-221 mm 7 mm lid recess Standard depth : 85 mm 20/25 mm knockouts to each compartment Manufactured from pre-galvanised steel to BS EN 10142 and 3, and polycarbonate/ABS 3 compartment contractor floor box 
1	CAV185	Floor box bases Supplied empty Lids and trims are detailed on p. 27 Outlet plates are detailed on p. 27 1 compartment floor box base Recommended hole cut-out size : 165-167 mm x 203-205 mm 85 mm deep 
1	CAV275	2 compartment floor box base Recommended hole cut-out size : 263-265 mm x 203-205 mm 75 mm deep
1	CAV285	85 mm deep
1	CAV2110 ¹	110 mm deep 

Pack	Cat. Nos.	Cavity floor boxes (continued)
1	CAV375	3 compartment floor box base Recommended hole cut-out size : 340-342 mm x 203-205 mm 75 mm deep
1	CAV385	85 mm deep
1	CAV3110 ¹	110 mm deep 
1	CAV475	4 compartment floor box base Recommended hole cut-out size : 340-342 mm x 203-205 mm 75 mm deep
1	CAV485	85 mm deep
1	CAV4110 ¹	110 mm deep 
1	SLAB1	Slab floor box 1 compartment
1	SLAB2	2 compartment
1	SLAB3	3 compartment
1	SLAB4	4 compartment 

1 : 110 mm deep base boxes not suitable for edge trim lids