

## MCBs DX<sup>3</sup> 10000 - 16 kA

thermal magnetic circuit breakers from 2 A to 125 A



4095 08

Dimensions **p. 12**  
 Technical information **p. 7-8**

Conform to IEC 60898-1  
 Breaking capacity  
 10000 - IEC 60898-1 - 400 V~  
 16 kA - IEC 60947-2 - 400 V~  
 Can be equipped with DX<sup>3</sup> auxiliaries and accessories **p. 6**

Pack	Cat. Nos.	MCBs DX <sup>3</sup> 10000 - 16 kA - D curve	
		<b>Single pole 230/400 V~</b>	
		D curve	Number of modules
1	4094 25	Nominal rating I <sub>n</sub> (A)	
1	4094 28	2	1
1	4094 30	6	1
1	4094 32	10	1
1	4094 33	16	1
1	4094 34	20	1
1	4094 35	25	1
1	4094 36	32	1
1	4094 37	40	1
1	4094 38	50	1
1	4094 38	63	1
		<b>Double pole 230/400 V~</b>	
1	4094 44	2	2
1	4094 47	6	2
1	4094 49	10	2
1	4094 51	16	2
1	4094 52	20	2
1	4094 53	25	2
1	4094 54	32	2
1	4094 55	40	2
1	4094 56	50	2
1	4094 57	63	2
1	4094 58	80	3
1	4094 59	100	3
1	4094 60	125	3
		<b>Triple pole 400 V~</b>	
1	4094 92	2	3
1	4094 95	6	3
1	4094 97	10	3
1	4094 99	16	3
1	4095 00	20	3
1	4095 01	25	3
1	4095 02	32	3
1	4095 03	40	3
1	4095 04	50	3
1	4095 05	63	3
1	4095 06	80	4.5
1	4095 07	100	4.5
1	4095 08	125	4.5
		<b>Four pole 400 V~</b>	
1	4095 26	2	4
1	4095 29	6	4
1	4095 31	10	4
1	4095 33	16	4
1	4095 34	20	4
1	4095 35	25	4
1	4095 36	32	4
1	4095 37	40	4
1	4095 38	50	4
1	4095 39	63	4
1	4095 40	80	6
1	4095 41	100	6
1	4095 42	125	6

## MCBs DX<sup>3</sup> 6000 - 10 kA

thermal magnetic circuit breakers from 1 A to 4 A



4079 65



4080 25

Dimensions **p. 12**  
 Technical information **p. 8**

Conform to IEC 60898-1  
 Breaking capacity  
 6000 - IEC 60898-1 - 400 V~  
 10 kA - IEC 60947-2 - 400 V~  
 Can be equipped with DX<sup>3</sup> auxiliaries and accessories **p. 6**

Pack	Cat. Nos.	MCBs DX <sup>3</sup> 6000 - 10 kA - D curve	
		<b>Single pole 230/400 V~</b>	
		D curve	Number of modules
1	4079 63	Nominal rating I <sub>n</sub> (A)	
1	4079 65	1	1
1	4079 66	3	1
1	4079 66	4	1
		<b>Double pole 230/400 V~</b>	
1	4080 23	1	2
1	4080 25	3	2
1	4080 26	4	2
		<b>Triple pole 400 V~</b>	
1	4080 81	1	3
1	4080 83	3	3
1	4080 84	4	3

Auxiliaries and accessories **p. 6**

