

# Atlantic metal enclosures

IP 55/IP 66 - IK 10 - Type 4x - Type 12



0369 19



0369 28



0369 79



0365 53

Enclosure and equipment selection chart **p. 6-7**  
 Technical information and dimensions **p. 12**

IP 66 according to standards IEC EN 60529 for 1-door enclosures - IP 55 according to standards IEC EN 60529 for 2-door enclosures

IK 10 according to standards IEC EN 62262

Excellent resistance to corrosion and chemical agents

80 µm thick textured polyester coating. Anti-corrosion treatment for hinges and pins

Reversible door - Fitted with lever

Double bar lock - Self-centering positioning system for the equipment

Compatible with all Atlantic accessories

| Pack | Cat. Nos.            |            | Metal enclosures                                   |                 |             |
|------|----------------------|------------|--|-----------------|-------------|
|      |                      |            | <b>Vertical version</b>                            |                 |             |
|      | Metal door           | Glass door | External dimensions (mm)<br>Height x Width x Depth | Number of doors | Weight (kg) |
| 1    | 0369 10 <sup>1</sup> |            | 300 x 200 x 160                                    | 1               | 3.9         |
| 1    | 0369 12 <sup>1</sup> |            | 400 x 300 x 160                                    | 1               | 6.3         |
| 1    | 0369 13              |            | 500 x 400 x 160                                    | 1               | 10.3        |
| 1    | 0369 17              | 0369 27    | 400 x 300 x 200                                    | 1               | 6.9         |
| 1    | 0369 18              | 0369 28    | 500 x 400 x 200                                    | 1               | 11.2        |
| 1    | 0369 19              | 0369 29    | 600 x 400 x 200                                    | 1               | 13          |
| 1    | 0369 20              |            | 600 x 500 x 200                                    | 1               | 16.8        |
| 1    | 0369 21              |            | 700 x 500 x 200                                    | 1               | 20.3        |
| 1    | 0369 25              |            | 500 x 400 x 250                                    | 1               | 13.2        |
| 1    | 0369 26              | 0369 36    | 600 x 400 x 250                                    | 1               | 14          |
| 1    | 0369 30              | 0369 40    | 700 x 500 x 250                                    | 1               | 23.8        |
| 1    | 0369 31              | 0369 41    | 800 x 600 x 250                                    | 1               | 30.9        |
| 1    | 0369 32              |            | 1000 x 600 x 250                                   | 1               | 44.5        |
| 1    | 0369 33              |            | 1000 x 800 x 250                                   | 1               | 49.5        |
| 1    | 0369 37              | 0369 47    | 800 x 600 x 300                                    | 1               | 32          |
| 1    | 0369 38              | 0369 48    | 1000 x 600 x 300                                   | 1               | 45          |
| 1    | 0369 39              | 0369 49    | 1000 x 800 x 300                                   | 1               | 56.9        |
| 1    | 0369 42              |            | 1200 x 600 x 300                                   | 1               | 50.4        |
| 1    | 0369 43              |            | 1200 x 800 x 300                                   | 1               | 67          |
| 1    | 0369 44              |            | 800 x 600 x 400                                    | 1               | 41.6        |
| 1    | 0369 45              |            | 1000 x 800 x 400                                   | 1               | 63.5        |
| 1    | 0369 46              | 0369 56    | 1200 x 800 x 400                                   | 1               | 73.6        |
| 1    | 0369 50              | 0369 60    | 1400 x 800 x 400                                   | 1               | 81.6        |
|      |                      |            | <b>Square version</b>                              |                 |             |
| 1    | 0369 51 <sup>1</sup> |            | 300 x 300 x 160                                    | 1               | 4.8         |
| 1    | 0369 55              |            | 300 x 300 x 200                                    | 1               | 5.6         |
| 1    | 0369 57              |            | 400 x 400 x 200                                    | 1               | 8.7         |
| 1    | 0369 59              |            | 500 x 500 x 200                                    | 1               | 13.6        |
| 1    | 0369 62              |            | 500 x 500 x 250                                    | 1               | 15.2        |
| 1    | 0369 64              | 0369 74    | 600 x 600 x 250                                    | 1               | 22.8        |
| 1    | 0369 68              |            | 800 x 800 x 300                                    | 1               | 48          |
| 1    | 0369 72              |            | 600 x 600 x 400                                    | 1               | 33.5        |
|      |                      |            | <b>Horizontal version</b>                          |                 |             |
| 1    | 0369 11 <sup>1</sup> |            | 300 x 400 x 160                                    | 1               | 6.2         |
| 1    | 0369 75              |            | 300 x 400 x 200                                    | 1               | 6.9         |
| 1    | 0369 76              |            | 400 x 600 x 200                                    | 1               | 13          |
| 1    | 0369 77              |            | 400 x 600 x 250                                    | 1               | 14          |
| 1    | 0369 78              |            | 600 x 800 x 300                                    | 2               | 38.4        |
| 1    | 0369 79              |            | 600 x 1000 x 300                                   | 2               | 47.4        |
| 1    | 0369 80              |            | 800 x 1000 x 300                                   | 2               | 59.7        |
| 1    | 0369 81              |            | 1000 x 1200 x 300                                  | 2               | 85.7        |

1 : Without cable entries plate

| Pack | Cat. Nos. | Roofs RAL 7035                              |            |             |
|------|-----------|---|------------|-------------|
|      |           | Steel                                       |            |             |
|      |           | Possible adjustment ± 20 mm (front or back) |            |             |
|      |           | For enclosures                              |            |             |
|      |           | Width (mm)                                  | Depth (mm) | Weight (kg) |
| 1    | 0365 51   | 300   | 200        | 1.2         |
| 1    | 0365 52   | 400   | 200        | 1.4         |
| 1    | 0365 67   | 500   | 200        | 1.8         |
| 1    | 0365 68   | 600   | 200        | 2.1         |
| 1    | 0365 53   | 400   | 250        | 1.8         |
| 1    | 0365 64   | 500   | 250        | 2           |
| 1    | 0365 54   | 600   | 250        | 2.5         |
| 1    | 0365 56   | 600   | 300        | 3           |
| 1    | 0365 57   | 800   | 300        | 3.6         |
|      |           | <b>Plinths RAL 7021</b>                     |            |             |
|      |           | Height 200 mm                               |            |             |
|      |           | Front and rear trap door                    |            |             |
|      |           | For enclosures                              |            |             |
|      |           | Width (mm)                                  | Depth (mm) | Weight (kg) |
| 1    | 0363 00   | 600   | 300        | 6           |
| 1    | 0363 01   | 800   | 300        | 6.7         |

Lina 12.5 and Lina 25 perforated plates, **p. 21**

