


PRODUCT IMAGES ARE ONLY ILLUSTRATIVE



Stirrup hanger
MGR44HE



Fastener kit 2
WSTIPFIX2

Order information (p. 6)
Standards and quality assessment (p. 11)
Dimensions and technical information (p. 12-17)

Pack	Cat. Nos.	Accessories
1	MGR44H F	Stirrup hangers Hole for M10 rod It is suggested to order finish E (powder coated) and specify CPC (clear powder coating) 100 mm wide x 100 mm max. depth For use with IP55 trunking 50 mm width
1	MGR66H F	150 mm wide x 150 mm max. depth For use with IP55 trunking 75 mm and 100 mm widths
1	MGR99H F	225 mm wide x 225 mm max. depth For use with IP55 trunking 150 mm width
1	MGR1212H F	225 mm wide x 225 mm max. depth For use with IP55 trunking 225 mm width
10	MGR44OH F	Overhead hangers For use with IP55 trunking It is suggested to order finish E (powder coated) and specify CPC (clear powder coating) For use with IP55 trunking 50 mm width
10	MGR66OH F	For use with IP55 trunking 75 mm and 100 mm widths
1	T206	PVC edging strip For fitting on to top edge of divider 10 m strip

Pack	Cat. Nos.	Fasteners and tools
1	WSTIPFIX1	Spare fixing kits Supplied with coupler – 50 mm and 75 mm - M5 x 10 mm tamperproof screws x 6 - M5 x 16 mm tamperproof screws x 4 - earth link x 1
1	WSTIPFIX2	Supplied with coupler – 100 mm, 150 mm and 225 mm - M5 x 10 mm tamperproof screws x 12 - M5 x 16 mm tamperproof screws x 4 - earth link x 2
1	WSTIPFIX3	Supplied with trunking lids - M5 x 12 mm tamperproof screws x 14
1	TX25	Tools TORX®1 head screwdriver
10	TX25BIT	TORX®1 head 25 bit

Key :
 For finishes available for stirrup and overhead hangers
F = Finish **PG** (pre-galvanised)
 G (hot dip galvanised after manufacture)
 E (powder coated)

1 : TORX® is a registered trademark of Acument Intellectual Properties LLC