


Viking 3 heavy duty terminal blocks

for copper and aluminium cables




Technical characteristics p. 67


| Pack | Cat. Nos. | Heavy duty terminal blocks | | |
|------|-----------|---|---|------------|
| | | For copper and aluminium cables | | |
| | | IK 04 Conform to IEC 60947-7-1, EN 60947-7-1 UL 1059 and 486 E - CSA 22-2 Fire resistant IEC 60695-2-11 : 960°C (except cover) V2 according to UL 94 Bridging the gap between the enclosure and external cables Fixed using metal clip for rails 15 mm depth and EN 60715, 15 mm depth or on plate with screws Fitted with hinged covers with cut-outs Permits the use of CAB 3 markers Test via test plug Ø4 mm closed covers Blocks with identical width can be joined using a threaded rod Supports shunt with Cat. Nos. 0394 46/47 | | |
| 5 | 0390 10 | Cable - Cable Rigid or flexible connecting cable (mm ²) | Rigid or flexible connecting cable (mm ²) | Width (mm) |
| 5 | 0390 11 | Al/Cu 35 to 120 | Cu 35 to 70 | 42 |
| | | Al/Cu 70 to 300 | Cu 70 to 150 | 55 |
| | | Cable lug - Cable lug | | |
| | | Connecting plate max. (mm ²) | Connecting plate max. (mm ²) | Width (mm) |
| 5 | 0390 13 | Al/Cu 95 | Al/Cu 95 | 36 |
| 5 | 0390 14 | Al/Cu 150 | Al/Cu 150 | 42 |
| 5 | 0390 15 | Al/Cu 300 | Al/Cu 300 | 55 |
| | | Cable lug - Cable | | |
| | | Connecting plate max. (mm ²) | Rigid or flexible connecting cable (mm ²) | Width (mm) |
| 5 | 0390 17 | Al/Cu 150 | Cu 35 to 95 | 42 |
| 5 | 0390 18 | Al/Cu 300 | Cu 70 to 150 | 55 |

Termination options



Cable - Cable



Cable lug - Cable lug



Cable lug - Cable



| Pack | Cat. Nos. | Accessories |
|------|-----------|------------------------------------|
| | | Shunt |
| 5 | 0394 46 | For blocks with width 36 and 42 mm |
| 5 | 0394 47 | For blocks with width 55 mm |

DIN rails p. 58

