





Swifts® SS light duty cable tray

lengths and fittings (continued)







Selection charts **p. 12-13**
 Dimensions and technical information : lengths **p. 36** ; fittings **p. 38-45**
 Design notes **p. 118**
 Loading graphs **p. 36**


Pack	Cat. Nos.	Fittings (continued)
1	SSOR W F	90° outside risers For technical information, p. 40-41
1	SSOR W A F	60°, 45° and 30° outside risers For technical information, p. 40-41



Pack	Cat. Nos.	Fittings (continued)
1	SSAR W F	Adjustable risers For technical information, p. 42
1	SST W F	Equal tees For technical information, p. 43
1	SSX W F	4 way crosspieces For technical information, p. 44
1	SSR W K F	Straight reducers For technical information, p. 45



Additional gauges and finishes available to special order
Contact us on +44 (0) 345 605 4333



Key : selecting SS light duty fittings. Replace the letters shown in **red** with your choice from the following options :
W = Widths (mm) : **50, 75, 100, 150, 225, 300**
A = Angle (°) : **60, 45** and **30** (90 does not need to be included in order code)
F = Finish : **G** (hot dip galvanised after manufacture)
PG (pre-galvanised), **S** (stainless steel)
K = Narrowed width when using a reducer (mm) :
50, 75, 100, 150, 225