



# Swifts® XRF extra heavy duty return flange cable tray

lengths and fittings (continued)



Selection charts **p. 14-15**

Dimensions and technical information : lengths **p. 84** ; coupler sets **p. 85** ; fittings **p. 86-93**

Design notes **p. 118**

Loading graphs **p. 84**



Pack	Cat. Nos.	Fittings (continued)
1	XR FIR WF	All fittings have integral fishplates No couplers required <b>90° inside riser</b> For technical information, <b>p. 88-89</b>
1	XR FIR WAF	<b>60°, 45° and 30° inside riser</b> For technical information, <b>p. 88-89</b>
1	XR FOR WF	<b>90° outside riser</b> For technical information, <b>p. 88-89</b>
1	XR FOR WAF	<b>60°, 45° and 30° outside riser</b> For technical information, <b>p. 88-89</b>

Pack	Cat. Nos.	Fittings (continued)
1	XR FT WF	<b>Equal tees</b> For technical information, <b>p. 90</b>
1	XR FUT W B F	<b>Unequal tees</b> For technical information, <b>p. 91</b>
1	XR FX WF	<b>4 way crosspieces</b> For technical information, <b>p. 92</b>
1	XR FR W K F	<b>Straight reducers</b> For technical information, <b>p. 93</b>



Additional gauges and finishes available to special order

Contact us on +44 (0) 345 605 4333



Key : selecting XRF extra heavy duty fittings. Replace the letters shown in red with your choice from the following options :

- W = Widths (mm) : 100, 150, 225, 300, 450, 600
- A = Angle (°) : 60, 45 and 30 (90 does not need to be included in order code)
- B = Branch width (mm) : 100, 150, 225, 300, 450
- F = Finish : G (hot dip galvanised after manufacture), D (deep galvanised), S (stainless steel)
- K = Narrowed width when using a reducer (mm) : 100, 150, 225, 300, 450