

RCBOs DX³ 6000 - 10 kA

residual current circuit breakers from 3 A to 63 A - AC type



4110 02



4111 49



4111 92

Dimensions **p. 12**
 Technical information **p. 7-8**

Conform to IEC 61009-1

Breaking capacity:

6000 - IEC 61009-1 - 10 kA / IEC 60947-2 for single pole + neutral, double and four pole

• AC type : detect AC component faults

Enhanced immunity to unwanted tripping in disturbed environments

Can be equipped with DX³ auxiliaries and accessories **p. 12**

Pack	Cat. Nos.	Single pole + neutral - 230 V \sim - C curve	
		Neutral on right-hand side	
		AC Type 10 mA	
		Nominal rating In (A)	Number of modules
1	C curve 4109 93	16	2
		AC Type 30 mA	
1	4109 97	3	2
1	4109 99	6	2
1	4110 00	10	2
1	4110 02	16	2
1	4110 03	20	2
1	4110 04	25	2
1	4110 05	32	2
1	4110 06	40	2
		AC Type 300 mA	
1	4110 21	6	2
1	4110 22	10	2
1	4110 24	16	2
1	4110 25	20	2
1	4110 26	25	2
1	4110 27	32	2
1	4110 28	40	2

Pack	Cat. Nos.	Double pole - 230 V \sim	
		AC Type 10 mA	
		Nominal rating In (A)	Number of modules
1	C curve 4111 49	10	4
1	4111 50	16	4
1	4111 51	20	4
		AC Type 30 mA	
1	4111 57	10	4
1	4111 58	16	4
1	4111 59	20	4
1	4111 60	25	4
1	4111 61	32	4
1	4111 62	40	4
1	4111 63	50	4
1	4111 64	63	4
		Four pole - 400 V\sim	
		AC Type 30 mA	
		Nominal rating In (A)	Number of modules
1	C curve 4111 85	10	4
1	4111 86	16	4
1	4111 87	20	4
1	4111 88	25	4
1	4111 89	32	4
1	4111 90	40	7
1	4111 91	50	7
1	4111 92	63	7
		AC Type 300 mA	
1	4112 04	10	4
1	4112 05	16	4
1	4112 06	20	4
1	4112 07	25	4
1	4112 08	32	4
1	4112 09	40	7
1	4112 10	50	7
1	4112 11	63	7