

Arteor™ electronic switches



Support frames and surround plates selection charts **p. 30, 32-35**
Load selection charts **p. 14**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Sensitive switches - 100/240 V~
1	5720 51	For controlling light sources by simply passing the hand in front of the switch (distance 5 mm) Up to 5 sensitive switches can be combined to control the same lighting circuit Supplied with LED indicator Square version ○ White - 2 modules ● Magnesium - 2 modules
1	5734 55	
1	5725 51	Round version ○ White - 2 modules ● Magnesium - 2 modules
1	5736 55	

Arteor™ motion sensors



Support frames and surround plates selection charts **p. 30, 32-35**
Load selection charts **p. 14**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Motion sensors
1		Measurement of luminosity threshold Adjustment of luminosity threshold and time delay Max. lux and min. time delay factory preset Recommended fixing height : 1 m IR detection 180° Adjustable luminosity threshold : 5 to 1275 lux Installation in back box min. depth 40 mm recommended 2 modules Range 8 m With neutral, 3 wire - 2000 W Operates : - 2000 W incandescent and halogen lamps 230 V~ - 1000 VA ELV halogen lamps with ferromagnetic or electronic transformer - 500 VA compact fluorescent lamps - 0 to 250 W for LEDs Settings modified on the device via thumbwheel or configuration tool Cat. Nos. 0882 30 and 0882 35 (refer to website) Time delay adjustable from 5 s to 30 min
1	5740 47	○ White ● Magnesium ● Champagne ● Soft Alu
1	5740 97	
1	5741 41	With neutral, 3 wire - 400 W Only 1 motion sensor per lighting circuit No possibility to add a push button to also control the lighting circuit Time delay adjustable from 10 s to 10 min Consumption 0-55 W on standby
1	5741 40	
1	5740 05	○ White ● Magnesium
1	5740 55	
1	5740 09	Without neutral, 2 wire Possibility to put 3 motion sensors in parallel No possibility to add a push button to also control the lighting circuit Time delay adjustable from 10 s to 10 min Consumption 0-02 W on standby
1	5740 59	
1	0401 49	Active power compensator Makes 2 wire electronic lighting control units without neutral compatible with all commercially-available loads (LED, compact fluorescent, ELV halogen with ferromagnetic or electronic ballast, 230 V halogen, fluorescent tube, incandescent) Consumption 0-4 W

