

Synergy® Sleek Design

single pole switches and dimmers



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack Cat. Nos. Single pole plate switches 10 AX - 250 V~

Conform to BS EN 60669-1
Flush mounting back box : min. 35 mm deep
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

2 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8320 01
1	8322 01
1	8324 01
1	8320 02
1	8322 02
1	8324 02

Single pole plate switches 20 AX - 250 V~

Conform to BS EN 60669-1
Flush mounting back box : min. 35 mm deep
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

2 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

3 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

4 gang - 2 way switch

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8321 31
1	8323 31
1	8325 31
1	8321 32
1	8323 32
1	8325 32
1	8321 33
1	8323 33
1	8325 33
1	8321 34
1	8323 34
1	8325 34

Single pole intermediate 10 AX - 250 V~

Conform to BS EN 60669-1
Flush mounting back box : min. 35 mm deep
Nominal plate dimensions : 86 x 86 mm

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8320 05
1	8322 05
1	8324 05

Single pole push switches 10 A - 250 V~

Conform to BS EN 60669-1
Flush mounting back box : min. 35 mm deep
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way push switch

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8320 07
1	8322 07
1	8324 07

Pack Cat. Nos. Push on/off rotary universal dimmers 5 W/300 W 100 - 240 V~ - 50/60 Hz

Conform to BS EN 60669-2-1
Flush mounting back box : min. 40 mm deep
Equipped with overvoltage and short-circuit protection
Screw terminals

For all types of lamps :

- dimmable LEDs : 5 W to 75 W
 - dimmable compact fluorescent lamps : 5 W to 75 W
 - halogen with ferromagnetic or electronic transformer : 5 VA to 300 VA
 - fluorescent tube - ballast : 5 VA to 300 VA
 - halogen and incandescent 230 V : 5 W to 300 W
- When switched on, gradually (2 seconds) lights up at the level set before last switch-off
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way push switch

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8321 51
1	8323 51
1	8325 51

Push on/off rotary dimmers 400 W 100 - 240 V~ - 50/60 Hz

Conform to BS EN 60669-1
Flush mounting back box : min. 35 mm deep
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way

- Brushed stainless steel
- Polished stainless steel
- Gold

2 gang - 2 way

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8321 56
1	8323 56
1	8325 56
1	8321 57
1	8323 57
1	8325 57

Push on/off rotary dimmers 1000 W 250 V~ - 50/60 Hz

Conform to BS EN 60669-1
- Flush mounting back box : min. 40 mm deep
- 60-1000 W (230 V)
- 60-500 W(127 V) for incandescent and halogen lamps 60-600 VA (230 V)
- 60-300 VA (127 V) for halogen lamps with electronic transformers 60-100 VA (230 V)
- 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers
Nominal plate dimensions : 86 x 86 mm

1 gang - 2 way push switch

- Brushed stainless steel
- Polished stainless steel
- Gold

Pack	Cat. Nos.
1	8321 50
1	8323 50
1	8325 50

Thermostat solutions
p. 16

