


# CX<sup>3</sup> power contactors without handle

16 A to 63 A



Technical information p. 44  
Dimensions p. 47

Conform to IEC/EN 61095  
Space for power supply busbar on top (up to 25 A)

Pack	Cat. Nos.	Power contactors with 24 V~ coil		
		<b>Double pole - 250 V~</b>		
1	4125 03	I max 16 A		Type of contact N/C + N/O Number of modules 1
1	4125 05	25 A		2 N/O 1
		<b>Power contactors with 230 V~ coil</b>		
		<b>Double pole - 250 V~</b>		
4	4125 21	I max 16 A		Type of contact N/C + N/O Number of modules 1
1	4125 24	25 A		2 N/C 1
		<b>Four pole - 400 V~</b>		
5	4125 35	25 A		4 N/O 2
1	4125 36	25 A		4 N/C 2
1	4125 33	25 A		2 N/C + 2 N/O 2

Pack	Cat. Nos.	Signalling auxiliaries for CX <sup>3</sup> contactors			
		Auxiliary changeover switch Used to signal the position status of the contacts on the product to which it is connected			
		<b>For 1 module contactors 16 A to 25 A</b> Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4124 29	I max 5 A	Voltage 250 V~	Contact N/C + N/O	Number of modules 0-5
		<b>For 2 module contactors 25 A</b> Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4124 30	5 A	250 V~	N/C + N/O	0-5
		<b>For 63 A contactors</b> Maximum 1 auxiliary device per contactor Fitted on left-hand side of contactor			
1	4124 31	5 A	250 V~	N/C + N/O	0-5
		<b>Accessory</b>			
10	4063 07	Spacing unit 0.5 module To be placed between every 2 contactors to aid cooling			

