



 Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with square rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	<b>Smarter connected thermostat</b>
1	0490 36	Allows you to adjust and monitor room temperature precisely and accurately; all programming and most functions are performed simply and intuitively using the dedicated app. Thanks to its Wi-Fi connection, Smarter can be programmed and controlled remotely; it can also display room temperature and humidity. The temperature level can be set locally for manual operation and the Boost function can be activated. Boost forces the switching on of the system for a limited time (30, 60 or 90 minutes) independent of the measured and programmed temperature - 100 ÷ 240 V~, 50/60 Hz power supply - 2 W max. absorption - maximum cable section 1 x 1.5 mm <sup>2</sup> - temperature measurement 5 ÷ 40 °C - temperature set-point 5 ÷ 40 °C - increase of 0.5 °C - 1-contact output in switching free of potential 5(2)A 2 modules Flush mounting Surface mounting
1	0490 37	

Pack	Cat. Nos.	<b>Thermostats</b>
1	5722 03	<b>Electronic room thermostat</b> Control knob with index and adjustable segments for min. and max. settings Adjustable range from 5 °C to 30 °C (+/- 0.5 °C) Power supply : 230 V~ - 50/60 Hz One potential free changeover contact output Suitable for controlling heated ceilings and underfloor heating - LV use breaking capacity : 8 A - 250 V~ - resistive inductive circuit 2 A - 250 V~ - inductive circuit - ELV use breaking capacity : 12 to 48 V~ - 12 to 24 V=, from 1 mA min. to 500 mA max. 2 modules <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5727 03	
1	5727 06	
1	5727 05	
1	5722 63	<b>Thermostat for electric floor heating</b> With one potential free N/O contact and LED 16 A - 230 V~ Adjustable range from 7 °C to 40 °C 2 modules <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5727 63	
1	5727 08	
1	5727 07	

Pack	Cat. Nos.	<b>Fan controllers</b>
1	5722 18	2 modules <b>Rotary speed controller for fan</b> Operates 40 to 400 VA limit switch For progressive speed control of ceiling fan <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5727 18	
1	5727 97	
1	5727 96	
5	5722 02	<b>Curtain switches</b> 1 module <b>Curtain switch centre off</b> <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
5	5727 02	
5	5700 52	
5	5710 52	
5	5722 01	<b>Curtain switch centre retract</b> <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
5	5727 01	
5	5727 55	
5	5727 54	
10	5722 19	<b>Electric roller blind controllers - 250 V~</b> <b>For control via automatic box (N/O mechanism)</b> Double push button - 10 A 2 modules <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
10	5727 19	
10	5729 43	
10	5729 42	
10	5722 20	<b>For direct control of a motor (mechanism with fixed positions)</b> Double switch - 10 A 2 modules <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
10	5727 20	
10	5700 54	
10	5710 54	
1	5723 60	<b>RCBO - 16 A - 230 V~</b> Single pole + neutral - 30 mA - 2 modules The RCBO is used to protect people (premises with a conductive floor, presence of water, etc...) against direct contact with live parts or leakages to earth With test button <ul style="list-style-type: none"> <li>○ White</li> </ul>


 Launched by Legrand in 2015, Eliot is a global programme designed to speed up the Internet of Things being rolled out in Legrand's offer. For availability and installation please contact our Technical Department on **+44 (0) 370 608 9020**