

Arteor™

rear pluggable data sockets, wiring splitters and adaptors



Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Rear pluggable RJ 45 sockets
		Certified as conforming to standards ISO 11801 ed. 2-0, EN 50173-1 and EIA/TIA 568 Contacts marked with 568 A and B dual colour code and numbers Connectors with self-stripping terminals Possibility of re-wiring in the event of error Multidirectional cable entry Used to create Cat. 6 and Cat. 5e links in accordance with standards. 2 modules
10	5723 31	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5728 31	
10 N	5729 10	
10 N	5729 09	
10	5723 33	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5728 33	
10 N	5729 12	
10 N	5729 11	

Pack	Cat. Nos.	Telephone/Ethernet wiring splitters
		Provide increased security against theft and damage to double connectors Provide a rate of 10/100 Mbps Multidirectional cable entry Can be installed in all supports min. depth 35 mm Telephone and Ethernet applications marked on the protective cap. 1 module
		UTP - double connector 8 contacts
10	5723 35	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5728 35	
10 N	5729 28	
10 N	5729 27	

Pack	Cat. Nos.	Adaptors for Keystone data sockets
		Equipped with transparent label holder
		Single connector 2 modules
10	5723 37	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5728 37	
10 N	5729 32	
10 N	5729 31	

Pack	Cat. Nos.	Adaptors for Systimax ¹ data sockets
		Equipped with transparent label holder
		Single connector 2 modules
10	5723 38	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5728 38	
10 N	5729 34	
10 N	5729 33	

1 : Systimax® is a registered trademark of CommScope Inc.

Arteor™

USB data sockets



Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	USB data sockets for data transfer
		Used to bring connections closer to the user For connecting USB devices (interactive white board, scanner-printer, external hard disk)
		Preterminated - USB 3-0 Maximum length : 5 m Recommended cable : USB Type-A Equipped with a 15 cm cord 1 module
1	5720 94	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5725 94	
1 N	5725 76	
1 N	5725 75	
		Connection via screw terminals - USB 2-0 Maximum length : 5 m Recommended cable : USB Type-A Cross-section : 1 mm ² 1 module
1	5722 75	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5727 75	
1 N	5725 53	
1 N	5725 52	