



7300 90



6781 38



7300 89



7300 69



7300 59



7300 78

Front plates : white thermoset
Terminal screws captive and backed off ready for cabling
Supplied with faceplate screw caps

Pack	Cat. Nos.	Shaver socket
1	7300 90	<p>Conform to BS EN 61558-2-5 : 1998 IP 24</p> <p>For use with European, British, American and Australian 2 pin plugs Screwless live and neutral terminals Double wound isolating transformer Automatic self-resetting overload feature Plug insertion operates microswitch which energises transformer Flush mounting back box : min. 47 mm deep Nominal plate dimensions : 146 x 86 mm</p> <p>Supply : 230 V - 50/60 Hz Output : 230/120 V - 20 VA max.</p>

Pack	Cat. Nos.	RCD sockets 13 A - 250 V~
1	6781 33	<p>Conform to BS 7288 : 1990 and BS 1363 - Part 2 : 1995 Conventional earth pin release shutter Maximum operating current 16 A Incorporate a 'test and reset' button Flush mounting back box : min. 25 mm deep</p> <p>DP 30 mA - active - trips in the event of a power failure - suitable in applications where automatic restoration of supply would be hazardous, e.g. machinery, power tools Nominal plate dimensions : 86 x 86 mm</p>
1	6781 37	<p>RCD unit 1 gang DP 30 mA active</p> <p>Nominal plate dimensions : 86 x 146 mm</p>
1	6781 34	<p>RCD unit 2 gang DP 30 mA active</p> <p>DP 30 mA - passive - does not trip in the event of a power failure - suitable in applications where automatic restoration of supply is required, e.g. fridge, freezer, unmanned areas Nominal plate dimensions : 86 x 86 mm</p>
1	6781 38	<p>RCD unit 1 gang DP 30 mA passive</p> <p>Nominal plate dimensions : 86 x 146 mm</p>
1	6781 38	<p>RCD unit 2 gang DP 30 mA passive</p>

Pack	Cat. Nos.	Socket outlets 15 A - 250 V~
		<p>Conform to BS 546 : 1950 Optional red LED 'power on' upgrade pack available (p. 54) Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm</p>
10	7300 88	<p>1 gang - unswitched</p>
10	7300 89	<p>1 gang - switched</p>

Pack	Cat. Nos.	Socket outlets 5 A - 250 V~
		<p>Conform to BS 546 : 1950 Optional red LED 'power on' upgrade pack available (p. 54) 2 earth terminals Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm</p>
10	7300 68	<p>1 gang - unswitched</p>
10	7300 69	<p>1 gang - switched</p>

Pack	Cat. Nos.	Socket outlet 2 A - 250 V~
		<p>Conform to BS 546 : 1950 Optional red LED 'power on' upgrade pack available (p. 54) Conventional earth pin shutter release Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm</p>
10	7300 59	<p>1 gang - unswitched</p>

Pack	Cat. Nos.	Switched USB sockets
		<p>Conform to BS 1363-2 USB chargers conform to BS EN 60950-1</p>
1	7300 78	<p>1 gang switched - single pole USB Type-A 2.4 A - 5 V = - 12 W Consumption in passive mode < 0.08 W Nominal plate dimensions : 86 x 86 mm</p>
1	7300 78	<p>1 gang - switched</p>
1	7300 79	<p>2 gang switched - single pole USB Type-A + Type-C 3 A - 5 V = - 15 W Consumption in passive mode < 0.08 W Nominal plate dimensions : 86 x 146 mm</p>
1	7300 79	<p>2 gang - switched</p>

Flush and surface mounting back boxes p. 55



Red power indicator LED pack p.54