

Synergy® Authentic

single pole switches and dimmers



Slim front plate :

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Single pole plate switches 10 AX - 250 V~

Pack	Cat. Nos.	1 gang - 1 way switch
1	8330 00	● Brushed stainless steel
1	8332 00	● Polished stainless steel
1	8334 00	● Gold
1 gang - 2 way switch		
Nominal plate dimensions : 86 x 86 mm		
1	8330 01	● Brushed stainless steel
1	8332 01	● Polished stainless steel
1	8334 01	● Gold
1 gang - intermediate switch		
Nominal plate dimensions : 86 x 86 mm		
1	8330 05	● Brushed stainless steel
1	8332 05	● Polished stainless steel
1	8334 05	● Gold
2 gang - 2 way switch		
Nominal plate dimensions : 86 x 86 mm		
1	8330 02	● Brushed stainless steel
1	8332 02	● Polished stainless steel
1	8334 02	● Gold
3 gang - 2 way switch		
Nominal plate dimensions : 86 x 86 mm		
1	8330 03	● Brushed stainless steel
1	8332 03	● Polished stainless steel
1	8334 03	● Gold
4 gang - 2 way switch		
Nominal plate dimensions : 86 x 146 mm		
1	8330 04	● Brushed stainless steel
1	8332 04	● Polished stainless steel
1	8334 04	● Gold

Single pole push switches 10 A - 250 V~

Pack	Cat. Nos.	1 gang - 2 way push switch
1	8330 07	● Brushed stainless steel
1	8332 07	● Polished stainless steel
1	8334 07	● Gold

Single pole plate switches 20 AX - 250 V~

Pack	Cat. Nos.	1 gang - 2 way switch
1	8331 31	● Brushed stainless steel
1	8333 31	● Polished stainless steel
1	8335 31	● Gold

Single pole plate switches 20 AX - 250 V~

Pack	Cat. Nos.	2 gang - 2 way switch
1	8331 32	● Brushed stainless steel
1	8333 32	● Polished stainless steel
1	8335 32	● Gold
3 gang - 2 way switch		
Nominal plate dimensions : 86 x 86 mm		
1	8331 33	● Brushed stainless steel
1	8333 33	● Polished stainless steel
1	8335 33	● Gold
Push on/off rotary universal dimmer 5 W/300 W		
Conform to BS EN 60669-2-1		
Flush mounting back box : min. 40 mm deep		
Equipped with overvoltage and short-circuit protection		
Screw terminals. For all types of lamps :		
- dimmable LEDs : 5 W to 75 W		
- dimmable compact fluorescent lamps : 5 W to 75 W		
- halogen with ferromagnetic or electronic transformer : 5 VA to 300 VA		
- fluorescent tube - ballast : 5 VA to 300 VA		
- halogen and incandescent 230 V : 5 W to 300 W		
When switched on, gradually (2 seconds) lights up at the level set before last switch-off		
Nominal plate dimensions : 86 x 86 mm		
1 gang - 2 way push switch		
1	8331 51	● Brushed stainless steel
1	8333 51	● Polished stainless steel
1	8335 51	● Gold

Push on/off rotary dimmer 400 W 100-240 V~ - 50/60 Hz

Pack	Cat. Nos.	1 gang - 2 way
1	8331 56	● Brushed stainless steel
1	8333 56	● Polished stainless steel
1	8335 56	● Gold
2 gang - 2 way		
1	8331 57	● Brushed stainless steel
1	8333 57	● Polished stainless steel
1	8335 57	● Gold

Push on/off rotary dimmer 1000 W 100-240 V/50-60 Hz

Pack	Cat. Nos.	1 gang
1	8331 50	● Brushed stainless steel
1	8333 50	● Polished stainless steel
1	8335 50	● Gold

Thermostat solutions
p. 16

