


Mylinec™
Ref . No. : 675968
Switch 25A 1M 1W SP with Indicator-White
Date : 27-06-23
Rev.2

1. Use

General lighting control mechanism

2.Type

Switch 25A 1M 1W SP with Indicator

No. of modules : 1

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 28 mm

Height : 57.2 mm

Depth : 40 mm

Weight (g) : 25

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6mm²

Stripping : 10mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch operating mechanically by rocker toggling

6.TECHNICAL CHARACTERISTICS
6.1 Material Characteristics

Rocker : Polycarbonate

Lens : Polycarbonate Red

Base : Polypropylene

Front Cover : Polycarbonate

Contact Terminal : Brass

Pivot Terminal : Brass

Screws : Steel with zinc plating

Rocker spring : Stainlesssteel

Plunger : PA 66+20% SI + PTFE

Contact Tip : Silver

Moving Contact : Copper with silver Tip

6.2 Electricals Characteristics

Voltage : 230V AC

Current : 25A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854