

Synergy® Sleek Design

British standard socket outlets and USB sockets



8320 75



8322 61



8324 89



8320 44



8324 78



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Socket outlets 13 A - 250 V~
1	8320 65	<p>Conform to BS EN 1363: Part. 2 With safety shutter mechanism Flush mounting back box : min. 35 mm deep ASTA licence</p> <p>1 gang unswitched Nominal plate dimensions : 86 x 86 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 65	
1	8324 65	
1	8320 75	<p>2 gang unswitched Nominal plate dimensions : 86 x 146 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 75	
1	8324 75	
1	8320 60	<p>Double pole socket outlets 13 A - 250 V~ Conform to BS EN 1363: Part. 2 With safety shutter mechanism Flush mounting back box : min. 35 mm deep ASTA licence</p> <p>1 gang switched Nominal plate dimensions : 86 x 86 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 60	
1	8324 60	
1	8320 61	<p>1 gang switched with blue LED power indicator Nominal plate dimensions : 86 x 86 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 61	
1	8324 61	
1	8320 70	<p>2 gang switched Nominal plate dimensions : 86 x 146 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 70	
1	8324 70	
1	8320 71	<p>2 gang switched with blue LED power indicators Nominal plate dimensions : 86 x 146 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 71	
1	8324 71	

Pack	Cat. Nos.	Socket outlets 15 A - 250 V~
1	8320 89	<p>Conform to BS 546 Patented 3 pin safety shutter mechanism Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm</p> <p>1 gang switched</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 89	
1	8324 89	
1	8320 69	<p>Socket outlets 5 A - 250 V~ Conform to BS 546 Patented 3 pin safety shutter mechanism Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm</p> <p>1 gang switched - single pole</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 69	
1	8324 69	
1	8320 59	<p>Socket outlets 2 A - 250 V~ Conform to BS 546 Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm</p> <p>1 gang unswitched</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 59	
1	8324 59	
1	8320 44	<p>Double USB sockets Conform to IEC 62684 Flush mounting back box : min. 40 mm deep Input voltage : 110 V/ 230 V 5 V (output) - 2400 mA Wiring with 1.5 mm² and 2.5 mm² (only live and neutral) Nominal plate dimensions : 86 x 86 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 44	
1	8324 44	
1	8320 78	<p>Switched USB sockets Conform to BS 1363-2 USB chargers conform to BS EN 60950-1</p> <p>1 gang switched - single pole USB Type-A 2.4 A - 5 V= - 12 W Consumption in passive mode < 0.08 W Nominal plate dimensions : 86 x 86 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 78	
1	8324 78	
1	8320 79	<p>2 gang switched - single pole USB Type-A + Type-C 3 A - 5 V= - 15 W Consumption in passive mode < 0.08 W Nominal plate dimensions : 86 x 146 mm</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 79	
1	8324 79	