



 PRODUCT TECHNICAL DATA SHEET		
Myrius NEXTGEN™	Ref . No. :679366/ 679381	
Gateway + Home away Electronic switch	Date : 06-10-2021	Rev.1
		
Note : This product is a connected accessory which requires you to install the "Legrand connected (IoT) range" connected starter pack first.		
1. USE This pack enables you to create a connected installation in your home. It can be used to control lighting, roller shutters and electrical equipment plugged into connected products - using your smartphone and the Home + Control app - using voice assistants - from the general control at the entrance to your home		
2.Type IoT Gateway No. of modules : 2M Colour : White / Charcoal Grey Mounting : Flush box and Surface box - mounted IoT Master home away wireless switch No. of modules : Monoblock Colour : White / Charcoal Grey Mounting : Fixes directly on the wall or screws onto a flush-mounting box. Fits on a piece of furniture (movable).		
3.OVERALL DIMENSIONS Gateway- Width : 45 mm Height : 45 mm Depth : 46 mm Weight (g) : 44 Master home away wireless switch - Length : 86 mm Width : 86 mm Height : 12 mm Weight (g) : 218		
4.CONNECTION Gateway - wire terminal with screws Master home away wireless switch - Through wireless network		
5.OPERATION <div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>LED indicator: - useful during installation</p> <p>RESET button used to return to factory settings</p> </div> <div style="text-align: center;">  <p>RESET button used to return to factory settings</p> </div> </div> <p>Arrival scenario when pressed at the top: By default, switches on the connected sockets Can be customized with the Home + Control app</p> <p>LED indicator: - useful during installation - when pressed, burst flashes red if the battery power is low</p> <p>Leaving scenario when pressed at the bottom: By default, switches off all the lights in the installation Can be customized with the Home + Control app</p> <p>* Refer product instruction sheet</p>		
6.TECHNICAL CHARACTERISTICS 6.1 Material Characteristics Gateway Rocker : Acrylonitrile Butadiene Styrene (ABS) Base : Polycarbonate Mechanism : Electronic Master home away wireless switch Rocker : Acrylonitrile Butadiene Styrene (ABS) Mechanism casing : Polycarbonate Mechanism : Electronic Self-extinguishing: 650° C / 30 s.		
6.2 Electricals Characteristics Gateway Voltage: 100/240 V~ Standby consumption: 10 mA Master home away wireless switch Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day (tentative) ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN) Power level: < 100 mW		
6.3 Climate characteristics Storage temperature: 0° C to + 45° C Usage temperature: +5° C to + 45° C		
7.CARE Clean the surface with a cloth. Do not use acetone, tar-removing cleaning agents or trichloroethylene. Caution: Always test before using special cleaning products. Take care to recycle the battery appropriately. 		
8.CONFORMITY - APPROVALS Equipment Type Approval (ETA) through self-declaration issued under O.M. No. ETA-WPC /Policy/2018-19 dated 26 February, 2019		