


Myrius NEXTGEN™
Ref . No. : 679367/ 679382
Socket module with neutral
Date : 06-10-2021
Rev.1


Note : This product is a connected accessory which requires you to install the “**Legrand connected (IoT) range**” connected starter pack first.

1. USE

Connected socket module which can be controlled by a wireless lighting control and/or remotely via a smartphone, tablet or computer. Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app. Built-in protection against electrical overloads, for increased safety.

2.Type

IoT Socket module with neutral

No. of modules : 1

Colour : White / Charcoal Grey

Mounting : Flush box and Surface box - mounted

3.OVERALL DIMENSIONS

Width : 22.5 mm

Height : 45 mm


Depth : 45 mm

Weight (g) : 43

4.CONNECTION

Terminal : terminals with screws

5.OPERATION



* Refer product instruction sheet

6.TECHNICAL CHARACTERISTICS

6.1 Material Characteristics

Rocker : Acrylonitrile Butadiene Styrene (ABS)

Base : Polycarbonate

Mechanism : Electronic

850° C / 30 s for insulating parts holding live parts in place.

650° C / 30 s for the other insulating components.

6.2 Electricals Characteristics

Voltage: 100/240 V~

Current: 16 A

Power: 3680 W max.

Frequency: 50/60 Hz

Standby consumption: 0.1 mA

Delivered pre-wired 2.5 mm².

Cable length: 10 cm (cut phase)

Zigbee technology 2.4 GHz to 2.4835 GHz Power level: < 100 mW

Range: 200 m of unobstructed space 10 m between products

6.3 Climate characteristics

Storage temperature: 0° C to + 45° C

Usage temperature: +5° C to + 45° C

7.CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

8.CONFORMITY - APPROVALS

Equipment Type Approval (ETA) through self-declaration issued under O.M. No. ETA-WPC /Policy/2018-19 dated 26 February, 2019