MODBUS TABLE ORGANIZATION

MODDOS TADLE OKGANIZATIO	14						
Starting Address of the Group	Starting Address of the Group	System Version	System Version	Group Name (Text)	Group Code	Group Complexity	Group Version
Registers (Dec)	Registers (Hex)	(Release)	(Build)		(Hex)	(Hex)	(Hex)
16384	4000	01	11	State of Breaker	51 02	10	01 00
28672	7000	01	11	Differential Electric Protection	73 05	10	01 00
29184	7200	01	11	Three-phase Electric Protection	73 03	10	01 01
20480	5000	01	11	Three-phase Electric Measurement	71 03	30	01 00
32768	8000	01	11	Single-channel Thermal Measurement	81 00	10	01 00

MODBUS PROTOCOL DETAILS

Function Code (Dec)	Exception Codes (Dec)	Data Encoding
2 (Read Discrete Inputs)	1, 2, 3	"Big Endian" (most
		significant byte first)
4 (Read Input Registers)	1, 2, 3	"Big Endian" (most
		significant byte first)

MODBUS OVER SERIAL DETAILS

Physical Layer	Trasmission Modes	Device Addressing	Baud Rates (bit/s)	Data Bits	Data bits trasmission sequence	Parity	Stop Bits
standard EIA/TIA 485 (RS-485) two- wire configuration	RTU	1÷247	programmable (1200, 2400, 4800, 9600, 19200, 38400)	8	Least significant bit first	NONE	1

MASTER/SLAVE COMMUNICATION TIMING

Timer Description	Timer Value (msec)
Inter-character time-out	< 1,5 character times
Response delay (from master request)	-
Delay Time (between two master trasmissions)	-

REFER ALSO TO:

www.modbus.org

- MODBUS over serial line specification and implementation guide V1.02 - MODBUS APPLICATION PROTOCOL SPECIFICATION V1.1b

NOTE:

File and printed copies of this document are not subject to document change control.

File and printed copies of this document are not subject to document change control.

GENERAL

Register	Register	Register	Dimension	Description	Note	Read	Data
Number	Address	Address	[bit]			Function	Storing
	(Dec)	(Hex)				Codes (Dec)	
16385	16384	4000	3	State of Breaker			
16385	16384	4000	1	Open	The information reported here "self-resets" when the condition that generated it ends.	2	
16386	16385	4001	1	Closed	The information reported here "self-resets" when the condition that generated it ends.	2	
16387	16386	4002	1	Tripped	The information reported here "self-resets" when the condition that generated it ends.	2	
28673	28672	7000	5	Differential Electric Protection			
28673	28672	7000	1	Differential pre-alarm (>threshold I∆1)	The information reported here "self-resets" when the condition that generated it ends.	2	
28674	28673	7001	1	Differential alarm (>threshold $I\Delta 2$)	The information reported here "self-resets" when the condition that generated it ends.	2	
28675	28674	7002	2	RESERVED (return "0")			
28677	28676	7004	1	P. differential relay tripped	The information reported here is maintained even when the condition that generated it ends. The "reset" condition can	2	Y
					ONLY be the detection of the device in Closed state. It is therefore necessary that the switch state function is present; in		1
					case of the contrary, the relay Trip information MUST NOT BE IMPLEMENTED (Example: if the switch goes back to Open		1
					=> the Tripped Relay signal must be maintained up until the reset condition intervenes)		1
29185	29184	7200	9	Three-phase Electric Protection			
29185	29184	7200	1	Overload pre-alarm (threshold I1)	The information reported here "self-resets" when the condition that generated it ends.	2	1
29186	29185	7201	1	Overload pre-alarm (>threshold I2)	The information reported here "self-resets" when the condition that generated it ends.	2	1
29187	29186	7202	1	Over-temperature alarm (>threshold T)	The information reported here "self-resets" when the condition that generated it ends.	2	1
29188	29187	7203	1	RESERVED (returns "0")			
29189	29188	7204	1	Overload P. Relay Tripped (no phase indication)	 The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): the detection of the device in Closed state the detection of a minimum current value on the phases. 	2	Y
20100	20100	7205			The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the Tripped Relay signal must be maintained up until the reset condition intervenes)		, v
29190	29189	7205	1	Short circuit P. Relay Tripped (no phase indication)	 The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): the detection of the device in Closed state the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the Tripped Relay signal must be maintained up until the reset condition intervenes) 	2	Y
29191	29190	7206					Y
29192	29191	7207	1	RESERVED (returns "0")			
29193	29192	7208	1	Over-temperature P. Relay tripped	 The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): the detection of the device in Closed state the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the Tripped Relay signal must be maintained up until the reset condition intervenes) 	2	Ŷ

DISCRETE INPUT - Bits (R)

Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [bit]	Description	Note	Read Function Codes (Dec)	Write Function Codes (Dec)	Data Storing
				(no COILS availables)				

COILS - Bits (R&W)

Register Number 16385 16385	Register Address	Register	Dimension	Bit Position	Description						Read Function	
		Address	[word]			Туре	Scale	Unit	Range	Note	Code (Dec)	Data Storing
	(Dec)	(Hex)	6		Chate of Breaker							
	16384 16384	4000 4000	6	State of Breaker	State of Breaker RESERVED (returns error 84h)						4	Y
16386	16385	4001	1		Operations counter					Total value, may not be zeroed	4	Ý
16387	16386	4002	1		Maximum Number of Operations					Not configurable	4	Y
16388	16387	4003 4004	1		Breaker Features - Rated Current		1	A			4 4	Y Y
16389	16388	4004	1	3÷0	Breaker Features - Device Type and number of Poles Poles: number				1÷4		4	Ý Y
·				4	Poles: neutral position (left(1)/right(0))				111		4	Ý
				7÷5	RESERVED (returns"0")						4	Y
ł				8	Type of device: Isolating switch (0)/ Automatic (1)						4	Y
				9	Type of device: Repulsive Breaker (0)/Non Repulsive Breaker						4	Y
·				15÷10	RESERVED (returns "0")						4	Y
16390	16389	4005	1		Tripping Features - Breaking capacity		0,01	kA			4	Y
28673	28672	7000	7		Differential Electric Protection							, in the second s
28673 28674	28672 28673	7000 7001	1 4		Differential P. Relay (total) Tripped Counter RESERVED (returns "8000h")						4	Y
28678	28677	7005	1		G1 "main setting"– differential: levels			mA		Expressed as "numeric coding"	4	Y
28679	28678	7006	1		G1 – differential: times			msec		Expressed as "numeric coding"	4	Ý
29185	29184	7200	30		Three-phase Electric Protection							
29185	29184	7200	1		Overload P. relay (total) Tripped Counter (no phase indication)						4	Y
20105	20105	7201		1	Short circuit P. relay (total) Tripped Counter (no phase		1				4	Y
29186	29185	7201	1		indication)							
29187	29186	7202	1		Device Protection Relay (total) Tripped Counter ("III element",						4	Y
29188	29187	7203	1		no phase indications) RESERVED (returns "8000h")							
29189	29187	7203	1		Over-temperature P. Relay (total) Tripped Counter						4	Ý
29190	29189	7205	1		Last Release data Buffer: "Tripped" type reading only bit reply						4	
29190	25105	7205	Ŧ									
				0	Overload P. Relay Tripped Reply Short-circuit P. Relay Tripped Reply						4 4	┥────┦
				2	Device Protection Relay Tripped Reply ("III element")						4	1
				3	Earth Fault P. Relay Tripped Reply						4	
				4	Over-temperature P. Relay Tripped Reply						4	
ł				5 15÷6	Differential Tripped Reply RESERVED (returns "0")						4 4	┫─────┤
				15-0							4	
29191	29190	7206	2		Last Release data Buffer: Interrupted current or temperature			mA, °C		Expressed in "numeric coding"		
29193	29192	7208	1		G1 - overload: levels			A/%		Expressed in "numeric coding"	4	Y
29194 29195	29193 29194	7209 720A	1		G1 - overload: times G1 - overload: options			msec		Expressed in "numeric coding"	4	Y
29195	29194	720A	Ŧ	0	disabled(1)/active(0)						4	Y
				1	absolute value(1)/%In(0)						4	Ý
				4÷2	I2t=k MEM OFF(001)/I2t=k MEM ON(000)						4	Y
_					RESERVED (returns "0")						4	Y
29196	29195	720B	4	15÷8	point of work, Ir multiple RESERVED (returns "8000h")						4	Υ
29200	29195	720B	2		G1 – instant short circuit: levels			A/%		Expressed in "numeric coding"	4	Y
29202	29201	7211	1		G1 – instant short circuit: times			msec		Expressed in "numeric coding"	4	Y
29203	29202	7212	1	0	G1 – instant short circuit: options						4	Y
 		├		0	disabled(1)/active(0) absolute value(1)/%In(0)						4 4	Y Y
					curve t=k(001)/I2t=k(000)						4	Y
				7÷5	RESERVED (returns "0")						4	Ŷ
	20202			15÷8	Point of work for I2t curve, multiple of In			Λ /0/-			4	Y
29204 29206	29203 29205	7213 7215	2		G1 – device protection: levels G1 – device protection: times			A/% msec		Expressed in "numeric coding" Expressed in "numeric coding"	4 4	Y Y
29206	29205	7215	1	1	G1 – device protection: options		1				4 4	Y Y
				0	disabled(1)/active(0)						4	Ý
				1	absolute value(1)/%In(0)						4	Y
20200	20207	7017		15÷2	RESERVED (returns "0") RESERVED (returns "8000h")						4	Y
29208 29211	29207 29210	7217 721A	3		G1 – neutral protection: levels			%		Expressed in "numeric coding"	4	Y
29212	29210	721A 721B	1		G1 – neutral protection: options					Laprobled in Humene coung	4	Y
				0	disabled(1)/active(0)						4	Y
Г		1		1	"0" (%phase), valid for Overload protection, may be delayed and Instant Short Circuit						4	Y

Llegrand[®]

File and printed copies of this document are not subject to document change control.

INPUT REGISTERS - Words (R)

				4÷2 "0" (phase curve)				4	Y
				15÷5 RESERVED (returns "0")				4	Y
29213	29212	721C	1	G1 – over-temperature protection: levels		°C	Expressed in "numeric coding"	4	Y
29214	29213	721D	1	G1 – over-temperature protection: times		msec	Expressed in "numeric coding"	4	Y
20481	20480	5000	6	Three-phase Electric Measurement					
20481	20480	5000	1	Phase 1 Current Value (R)	unsigned integer	А	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20482	20481	5001	1	Phase 2 Current Value (S)	unsigned integer	А	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20483	20482	5002	1	Phase 3 Current Value (T)	unsigned integer	А	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20484	20483	5003	1	Neutral Current Value	unsigned integer	А	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20485	20484	5004	1	RESERVED (returns "8000h")					
20486	20485	5005	1	Differential Current Value	unsigned integer	mA	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
32769	32768	8000	1	Single-channel Thermal Measurement					
32769	32768	8000	1	Sensor 1 Temperature Value	signed integer	°C	Expressed in "numeric coding"	4	

Register	Register	Register	Dimension	Bit Position	Description	Туре	Scale	Unit	Range	Note	Read	Write	Data
Number	Address	Address	[word]								Function	Function	Storing
	(Dec)	(Hex)									Codes	Codes	
											(Dec)	(Dec)	
					(no HOLDING REGISTERS availables)								

HOLDING REGISTERS - Words (R&W)