

Data Sheet

Wall Exhaust Fan Kit with Duct and Grille - 100mm

CAT NO. EF100SQSWEKIT



A brand of **legrand**



EF100SQSWEKIT


Cat. No.	EF100SQSWEKIT
Description	Square Wall Exhaust Fan Kit with Duct and Grille, 100mm
Supply Voltage	230 - 240V a.c ~ 50 Hz
Power Rating	14W
Air Extraction	105m ³ /hr (Airflow depends on installation conditions)
Projection into wall	80mm (120mm with draft stopper)
Class of protection	Class II
IP Rating	IP24
Hole cut-out size	110mm
Fascia Size	158 x 158 X 17mm
Weight	450g (excl. packaging)
Time-delay	Compatible with HPM time-delay module EF 100/150TD
Sound Pressure Level at 3m	30dBA (Tested in accordance with AS 1217.5)
Warranty	3 Year

Wall Exhaust Fan Kit with Duct and Grille - 100mm

CAT NO. EF100SQSWEKIT




A brand of **legrand**



- Ideal for small bathrooms, kitchens and laundries.
- Kits includes: 1 External grille, 350mm X Ø100mm Duct, Ducting tape roll, Cable ties, Mounting screws, Instruction manual and Warranty card.
- Featuring an Axial flow fan which easily moves large volumes of air.
- Fitted with higher quality ball bearing motor for long lifespan, greater resistance to high temperatures and quieter operation.
- It encourages air circulation and steam reduction.
- Performance is higher when non-ducted.
- Wall mounting accessories included.

Kits includes:



Single Unit			
Cat No.	Barcode	Dimension (L X W X H)	Weight
EF 100SQSWEKIT	9321001491255	180 X 175 X 180mm	0.8kg

Outer Box (QTY 4)			
Cat No.	Barcode	Dimension (L X W X H)	Weight
EF 100SQSWEKIT	9321001491262	375 X 365 X 205mm	5.173kg

Legrand - Australia
1300 369 777
www.legrand.com.au
ABN 31 000 102 661

Legrand - New Zealand
0800 476 009
www.legrand.co.nz

Refer to your group buying office, Legrand Sales Representative or Legrand Sales Office for pricing.

Please note: specifications are subject to change without prior notice.