

EBDHS-B-MB-CB-DD | Casambi wireless, batten mount, high bay/high level, PIR presence detectors



Casambi Technology Explained:

The Casambi technology provides a mesh network where all the intelligence of the system is replicated in every node and, in such a way, creates a system with no single point of failure. In this kind of fully distributed architecture, any unit can go offline and catch up from others when they return back online.

Wireless Features:

- Control a large number of fixtures from any point
- Simple to use UI
- Wide range of functionality – Grouping Luminaires, different lighting situations for different occasions, colour temperature, daylight sensor, occupancy sensor and much more.


Sensor Features:

- Groundbreaking detection range up to 40m at a 15m mounting height
- Maximum mounting height up to 20m dependent on operating parameters
- Multi-pyro design offers greater sensitivity without false triggering
- Unique lens technology – high sensitivity within the detection range
- Built-in both switched relay and DALI dimming outputs
- Ideal for high bay applications, including warehouse lighting control
- IP40 rated
- Supplied with adjustable masking shields to tailor detection zones
- UK and international patents applied for
- 5 year warranty included
- Manufactured in the UK.

Technical Data


Part Code	EBDHS-B-MB-CB-DD
Weight	0.15kg
Supply voltage AC	100–240 VAC +/- 10%
Supply frequency (Hz)	50/60Hz
Rated current	10A
Terminal capacity	2.5mm ²
Max switched load:	
Incandescent lighting	10A
Fluorescent lighting	4A
Compact fluorescent lighting	4A
LED lighting	4A
Resistive heaters	10A
Load inrush rating	90A for 340µs
SON lighting	Switch loads via a contactor
Max DALI dim load	Up to 10 drivers
Cable specification	5 x 1mm ² solid core PVC sheath 90°C
Light detection range	1-999 lux
Transceiver frequency	2.4GHz ISM band
Transceiver power	Up to 4 dBm output power and -93 dBm RX sensitivity
Rated impulse voltage	2500V
Purpose	Sensing control
Operational temperature	0 to 50°C
Humidity	5 to 95% non-condensing
Material (casing)	Flame retardant ABS
Insulation class	Class 2
Cutout diameter	M20
IP rating	IP40
Compliance	CE UK CA

Accessories and Associated Products



Part Number	Description
 EBDHS-MS	Masking shields

Detection pattern

high < sensitivity > low



Dimensions (mm)



+44 (0)333 900 0671
 info@cpelectronics.co.uk
 www.cpelectronics.co.uk

connect with us

