

# Datasheet

## Inline Shower Round Fan Kit with Light-150mm

CAT. NO. EFLIL150SQWEKIT



A brand of legrand®



Class II construction


<b>Cat. No.</b>	<b>EFLIL150SQWEKIT</b>
<b>Description</b>	Inline Exhaust Fan Kit with a Light
<b>Nominal Supply Voltage</b>	230 - 240 V a.c. 50 Hz
<b>Power Rating</b>	60 W
<b>Lamp type</b>	LED MR16 (included)
<b>LED Lamp power supply</b>	12 V a.c. 50 Hz 5 W Max
<b>Driver</b>	60 VA, 12 V a.c. Electronic transformer with 1.8 m lead and connector
<b>Lamp replacement part number</b>	LMR16024K
<b>Draught stopper</b>	Yes (PET Sheet)
<b>Duct size</b>	5 m X Ø150 mm
<b>Engine size</b>	290 x 230 x 250 mm
<b>Engine weight</b>	3.0 kg
<b>Power cord length</b>	1 m
<b>Ceiling cut-out size (for inlet &amp; outlet grilles)</b>	Ø160 mm
<b>IP Rating</b>	IP55 - Engine only IPX3 - Lamp kit (ceiling installation)
<b>Warranty</b>	3 Years

# Inline Shower Round Fan Kit with Light- 150mm

CAT. NO. EFLIL150SQWEKIT




A brand of **legrand**



## FEATURES

- The inline fan is designed to extract steam and odours from a bathroom and expel it to the exterior through an eave outlet.
- It is also suitable for extracting air from one room and expelling it to another room (heat distribution).



Single Product (Qty 1)	
Cat. No.	Barcode
EFLIL150SQWEKIT	9321001496151

Max airflow* (m <sup>3</sup> /hr)		
Duct length	Low Speed (I)	High Speed (II)
No duct	450	555
1 m per side (total 2 m)	310	390
2.5 m per side (total 5 m)	270	335

\*Airflow depends on installation conditions.

## Specification for LED Lamp

Type	LED MR16
Lumens	480 lm
Efficacy	86 lm/W
CRI	80+
Light colour	3,000K Warm White Nominal
Beam angle	60°
Base	GU5.3

Legrand - Australia  
1300 369 777  
www.hpm.com.au  
ABN 31 000 102 661

Legrand - New Zealand  
0800 476 009  
www.hpm.co.nz

Refer to your group buying office, Legrand Sales Representative or Legrand Sales Office for pricing.

Please note: specifications are subjected to change without prior notice.