



Time delay switch surface-mounted

Cat. No(s): 0 860 62 - 0 861 62







0 860 62

1. USE


Lighting control mechanism.

2. RANGE

Description	Complete	Configurable
Time delay switch	0 860 62	0 861 62


Product with indicator:

Use bulb illuminated function providd by using bulb Cat. No 0 899 07





3. DIMENSIONS (mm)

Complete unit



Modular component






4. CONNECTION

■ 4.1 Connection

Type of terminals: with screws Terminals capacity: 2 x 2.5 mm² Option of two wires per terminal for tapping Stripping length: 7 mm

Screwdriver: Posidrive 1, Philips 1, flat 4 mm.

■ 4.2 WIRING



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 31D (complete product) Protection against impact: IK 04

■ 5.2 Material characteristics

Plate, frame, coverplate: Plastic Colour: White RAL 9003 UV resistant

Self-extinguishing:

- $+\ 850^{\circ}\ \text{C}\ /\ 30\ \text{s}$ for insulating parts holding live parts in place.
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 10 AX

Maximum power on integrated ballast lamps: 100 W Frequency: 50 Hz



■ 5.4 Climatic characteristics

Use and storage temperature: - 5° C to + 40° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

Lame



0 899 07 230 V Low power consumption green fluorescent

8. STANDARDS AND APPROVALS

Fiche technique: F00117EN/02

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Créée: 07/07/2003 | legrand

Mise à jour : 24/03/2021