



128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel.: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Two-way pull cord switch Surface-mounted



0 861 19



1. USE


Lighting control mechanism with pull-cord.

2. RANGE

Description	Complete	Configurable
Two-way pull-cord switch	0 860 19	0 861 19


3. DIMENSIONS (mm)

Complete unit



45

Modular component






4. CONNECTION

4.1 Connection

Type of terminals: with screws Terminals capacity: 2 x 2.5 mm² Option of two wires per terminal for tapping Stripping length: 7 mm Screwdriver: Posidrive 1, Philips 1, flat 4 mm.

■ 4.2 Wiring



5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 31D (complete product) Protection against impact: IK 04

5.2 Material characteristics

Plate, frame, coverplate: Plastic Colour: White RAL 9003 UV resistant

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place. + 650° C / 30 s for other parts made of insulating materials.

5.3 Electrical characteristics

Voltage: 250 V~ Current: 10 AX

Maximum power on integrated ballast lamps: 100 W Frequency: 50 Hz

■ 5.4 Climatic characteristics

Use and storage temperature: - 5° C to + 40° C



Two-way pull cord switch Surface-mounted

6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichlorethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

......

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES



Cat. No 0 898 05: Cord for pull-cord mechanisms - length: 1.5 m

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.