


Surface mounting two-way switch narrow version

Cat. No(s): 0 860 84/87 - 0 861 84/87





1. USE


Lighting control mechanism with or without marking components (locator light).

2. RANGE

Description	Complete	Configurable
Two-way switch	0 860 84	0 861 84
Two-way switch with indicator light	0 860 87	0 861 87


Indicator light product:

Light function possible using lamp Cat. No. 0 899 01/02/07.



3. DIMENSIONS (mm)

Complete






Configurable







4. CONNECTION

■ 4.1 Connection

Type of terminals: with screws Terminals capacity: 2 x 2.5 mm²


Option of two wires per terminal for tapping


Stripping length: 7 mm

Screwdriver: Posidrive 1, Philips 1, flat 4 mm.

■ 4.2 Wiring diagrams

0 860 84 - 0 861 84





5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 31D (complete product) Protection against impact: IK 04

■ 5.2 Material characteristics

Plate, frame, coverplate: Plastic Colour: White RAL 9003

UV resistant

Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place.
- + 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 10 AX

Maximum power on integrated ballast lamps: 100 W Frequency: 50 Hz



■ 5.4 Climatic characteristics

Use and storage temperature: - 5° C to + 40° C

Technical data sheet: F00143EN/02 Updated: 29/03/2021 Created: 04/02/2004

Surface mounting two-way switch narrow version

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

Lamps



0 899 01 12 V White incandescent - Power consumption 0.4 W 0 899 02 24 V White incandescent - Power consumption 0.8 W 0 899 07 230 V Low power consumption green fluorescent

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.