


Atlantic stainless steel cabinet

Cat. Nos : 0 352 00/01/02/03/05/06/11/13/14/15



CONTENTS

Page

1. General characteristics	1
2. Materials.....	1
3. Finishing.....	1
4. Range.....	2
5. Properties of stainless steel	2
6. Heat dissipation capacity.....	3
7. Overall dimensions	3
8. Effective surface areas	4
9. Fixing equipment.....	5
10. Equipment positioning.....	5
11. Equipment	6
12. Accessories.....	14

1. GENERAL CHARACTERISTICS

Stainless steel metal cabinets 304 L.

Protection index concerning protection from liquids and solid bodies:

- according to the IEC EN 60529 standard: IP 66 and IP 55 for two-door cabinets,
- according to the NEMA 250 standard: Type 4

Protection index IK 10 concerning protection against mechanical impact according to the IEC EN 62262 standard (EN 50102).

Approvals: UL type 4x, CSA, Bureau Veritas, LRS. LCIE No. 80257 - 575296.

CIEC 60721-3-4 classification:

- climatic conditions: 4K4,
- biological conditions: 4B1,
- presence of chemical agents: 4C3.

2. MATERIALS

Austenitic stainless steel casing (non-magnetic):

- 304 L <-> Z3 CN 18-9, 12-02
- Steels with the same composition are sometimes given different designations depending on the standards in force in their country of origin:

Country	Standards	Grade of steel
		Low-carbon grade austenitic alloy
United States	AISI	304 L
United States	UNS	S 30403
Europe	EN 10088-2 (1195)	X2CrNi18-9
Europe	Code number	1.4307
UK	BS 1554 (1990)	304 S 11
Germany	Previous standard	1.4307
France	NF A 35-573 (1990)	Z 3 CN 18-10
France	Previous standard	Z 2 CN 18-10
France	Ugine brand	NS 22 S
Sweden	MNC 900E (1985)	SIS 2352
Japan	JIS G 4304 (1987)	SUS 304 L

Door seal: 16 x 8 mm polyurethane foam.

3. FINISHING

Vertical brushed stainless steel: 180-grain polished (conform to NF E 05-015):


- $0.25 \mu\text{m} \leq Ra \leq 0.35 \mu\text{m}$,
- $2.5 \mu\text{m} \leq Rt \leq 4 \mu\text{m}$.

Upper and lower protective hoods.

Door with rounded vertical sides. Non-reversible door.

Closing by double bar lock(s):

- Epoxy finish,
- zamak-coated recess



4. RANGE**■ 4.1 Listed cabinets**

References	Dimension		
	Height	Width	Depth
0 352 00 ⁽¹⁾	300	200	160
0 352 01	400	300	200
0 352 02	500	400	
0 352 03	600		
0 352 05		250	
0 352 06	700		500
0 352 11	800	600	300
0 352 13	1000	800	
0 352 14	1200		
0 352 15	1400		

(1) Supplied complete with plain plate

■ 4.2 Custom cabinet on request**4.2.1 Open-back cabinets**

Back section cut away, leaving a 25 mm margin either with or without an equipment fixing area.

4.2.2 Cut-outs and drillings

On the body.

On the doors.

On plain plates.

Custom windows.

4.2.3 Equipement

Lina 12.5 or Lina 25 plain plates.

Fixing lugs.

Inner doors.

Fan installations.

4.2.4 Cable entry plates

Warning: adding a cable entry plate provides an IP55 protection index against liquids and solid bodies.

With or without cable entry.

Top/ Bottom positioning.

Installation of a Cabstop™ plate.

4.2.5 Closure

The universal closing fixtures provide a wide range of possible closing options.

Please contact us for individual configurations.

5. PROPERTIES OF STAINLESS STEEL**■ 5.1 Resistance to chemical agents**

ISI designation (indicative)	304 L ⁽¹⁾
ISO EN 10088-2 designation	1.4307
Standardized chemical composition	X2CrNi18-9
Chemical agents	
Fresh water, humid air	++
Slightly acidic distilled water	++
Salt water and spray	+
Ammonia water, all concentrations	++
Bleach (sodium hypochlorite) diluted to 0.3%	+
Lime potash (potassium hydroxide) 50%	++
Sodium potash (sodium hydroxide) 50%	++
Acetic acid - all concentrations	++
Concentrated vapours with condensation	+
Acetic acid < 50%	++
Citric acid > 50%	+
Lactic acid - all concentrations	++
Formic acid - all concentrations	++
Hydrochloric acid < 1%	-
Hydrochloric acid > 1%	--
Nitric acid < 90%	++
Nitric acid > 90%	+
Phosphoric acid - all concentrations	++
Sulphuric acid < 5%	+
Sulphuric acid 20%	-
Sulphuric acid 40%	--
Aliphatic hydrocarbons	++
Aromatic hydrocarbons	++
Alcohols	++
Glycols	++
Dry chlorinated solvents	+
Dry chlorinated solvents + moisture	-
Ketones	++
Terpenes	++

Resistance to chemical agents at ambient temperature with respect to a risk of exposure by sprinkling.

++ Excellent resistance (continuous exposure),

+ Good resistance (long exposure).

- Limited resistance (momentary exposure is possible),

-- Low resistance (exposure should be avoided).

(1) Avoid in the event of exposure to acidic foodstuffs such as white wine or mustard.

5. PROPERTIES OF STAINLESS STEEL (CONTINUED)

■ 5.2 Corrosion resistance

304 L stainless steel:

- to salt spray (BS) 1000 hrs
- to sulphur dioxide (SO₂) 500 hrs

■ 5.3 Environmental capacities

Climatic conditions		304 L
Inside	Dry	Excellent
	Damp	Excellent
	Damp and aggressive	OK
Outside	Rural	Excellent
	Urban	Excellent
	Industrial	OK
	Tropical	OK
	Marine	
Temperature and hygrometry	Cold	Excellent
	Very cold	Excellent
	Temperate (Europe)	Excellent
	Hot and dry (North Africa)	Excellent
	Damp	OK

■ 5.4 Use

In zones requiring rigorous hygiene, for example:

- food and beverage industries,
- distilleries,
- industrial kitchens,
- dairies,
- clean rooms.

In corrosive environments, for example:

- chemical industries,
- pharmaceutical industries,
- petroleum industries,
- paper industries.

304 L stainless steel resistance characteristics:

- nitric acid m 52 % at all temperatures and m 98 % cold
- cold-diluted organic acids,,
- salt solutions except chlorides, sulphides and sulphates,
- fresh water and natural atmosphere low in chlorides,
- foodstuffs except mustard and white wine.

6. HEAT DISSIPATION CAPACITY

Determined by testing the max. capacity of a cabinet to dissipate heat according to standard IEC 62208-1.

Configuration 1 (C1):

All outer surfaces of the cabinet are clear and not in contact with anything (floor standing, on stand or frame for example).

Configuration 2 (C2):

The rear surface is in contact with a wall, all other surfaces are clear (standard case of wall mounting for example).

For other installation configurations, please consult us.


References	Dimensions (mm)	Delta T (K)	Max. power that can be dissipated (W)	
			C1	C2
0 352 00	300 x 200 x 160	30	36	32
0 352 01	400 x 300 x 200	30	68	58
0 352 02	500 x 400 x 200	30	98	82
0 352 03	600 x 400 x 200	30	114	95
0 352 05	600 x 400 x 250	30	127	108
0 352 06	700 x 500 x 250	30	168	140
0 352 11	800 x 600 x 300	30	233	194
0 352 13	1000 x 800 x 300	30	347	283
0 352 14	1200 x 800 x 300	30	404	327
0 352 15	1400 x 800 x 400	30	518	428

7. DIMENSIONS (MM) SHEET STEEL

■ 7.1 Overall dimensions

Note: dimension C does not include the lock.

Lock thickness: 4 mm




Cabinet dimensions			Dimensions (mm)			
Height	Width	Depth	A	B	C	Q
300	200	160	301.6	199.6	161.5	
400	300	200	401.6	299.6	201.5	
500	400		501.6	399.6		250
600			601.6			350
700	500	250	702.4	500	251.5	400
800	600	300	802.4		301.5	500
1000	800		1003.6			600
1200				1203.6		800.6
	1000					
1400	800	400	1401	800.6	401.5	900

Sheet steel thickness:

- for height m 600 mm: 10/10e
- for height 700 and 800 mm: 12/10e
- for height M 1000 mm: 15/10e

8. EFFECTIVE SURFACE AREAS

8.1 Front panel





Cabinet dimension		Effective space (mm)	
Height	Width	Height	Width
300	200	262	160
400	300	362	260
500	400	462	360
600	400	562	360
700	500	662.4	460
800	600	762.4	560
1000	800	963	760
1200		1163	
1400		1360	

8.2 Plain plate door for 1-door cabinet (continued)

Cabinet dimension		Dimensions (mm)						Effective surface area (dm²)
Height	Width	A	B	C	D	E	Q	
300	200				256	153.5	centred	3.55
400	300	175		275	356	253.5		8.64
500	400	275		375	456	353.5	250	15.42
600	400	275		475	556	353.5	350	18.95
700	500	375	274	575	656	453.5	400	29.05
800	600	475	324	675	756	553.5		41.15
1000	800	675	424	875	956	754	600	71.38
1200			524	1075	1156		700	86.46
1400			624	1275	1350		900	100.55

8.2 Plain plate door for 1-door cabinet




Cabinets with H 500 and 600

Cabinets with H = 600

Locking points
- one only for H ≤ 400,
- 2 for H ≥ 500.
Direct closure by cam on each lock.

9. FIXING EQUIPMENT


Direct attachments: either Ø 9 screws or M8 studs.
Fixing lugs: see section 10.4 "Fixing lugs".



Cabinet dimension		Dimensions (mm)							
Height	Width	Cabinet back		Horizontal lugs		Vertical lugs		Maximum dimensions	
		E	F	T	U	R	S		
300	200	225	169	250	250	353	150	395	292
400	300	325	269	350	350	453	250	495	392
500	400	425	369	450	450	553	350	595	492
600	400	525	369	550	450	653	350	695	492
700	500	625	469	650	550	753	450	795	592
800	600	725	569	750	650	853	550	895	692
1000	800	925	769	950	850	1053	750	1095	892
1200		1125		1150		1253		1295	
1400	800	1325	769	1350	850	1450	750	1492	892


10. EQUIPMENT POSITIONING

■ 10.1 Fixing distances in the cabinet




Cabinet dimension		Dimensions (mm)	
Height	Width	F	E
300	200	225	125
400	300	325	225
500	400	425	325
600	400	525	325
700	500	625	425
800	600	725	525
1000	800	925	
1200		1125	725
1400	800	1325	725


■ 10.2 Fixing distances on the door



Cabinets with H 400



Cabinets with H 500 and 600




Cabinets with 1 door 700 ≤ H ≤ 1400

Cabinet		Dimensions (mm)				
Height	Width	A	B	C	D	E
300	200				256	153.5
400	300	175		275	356	253.5
500	400	275		375	456	353.5
600	400	275		475	456	353.5
700	500	375	274	575	656	453.5
800	600	475	324	675	456	553.5
1000	800	675	424	875	956	754
1200			524	1075	1156	
1400			624	1275	1350	750

10. EQUIPMENT POSITIONING (CONTINUED)


■ 10.3 Depth positioning




Cabinet depth	To cabinet back (mm)		Slide Cat. No.	Positioning with slides (mm)			
	J	K		M		N	
				min.	max.	min.	max.
160	140	125					
200	180	165					
250	230	215	0 367 43	93	213	78	198
300	280	265	0 367 44		263		248
400	380	365	0 367 45		363		348

11. EQUIPEMENT


■ 11.1 Direct mounting of equipment at back of cabinet (M8 screws)



- or slide with M8 nut adjustment (optional)



Equipment adjustment
Possible for 600 x 600 cabinet and beyond.
With Cat. No. 0 367 43/44/45.
Set of 4 slides for cabinet depths 250, 300 and 400.




11. EQUIPEMENTS (CONTINUED)


■ 11.2 Lina 12.5 and Lina 25 plain plates

- Galvanised steel plain plates and Lina 12.5
- Lina 12.5: with holes for the installation of equipment without marking, automatic alignment.
- Lina 25: zinc-plated steel.

Lina 12.5



Lina 25




■ 11.2 Lina 12.5 and Lina 25 plain plates (continued)


• Dimensions

Lina 12.5 plain plates and Lina 25 perforated plates.


Plain



Lina 12.5 details



Lina 25 perforated details



11. EQUIPEMENTS (CONTINUED)

■ 11.2 Lina 12.5 and Lina 25 plain plates (continued)

• Dimensions (continued)


Lina 12.5 plain plates and Lina 25 perforated plates

Cabinets		Lina 12.5 or Lina 25 plain plates		Effective surface area for equipment (dm ²)	Mounting of plates		Plain	Lina 12.5	Lina 25
Height	Width	G	H		F	E	Cat. No.	Cat. No.	Cat. No.
300	200	256	156	4.2	225	125		0 360 00	0 360 07
400	300	356	256	8.2	325	225	0 360 52	0 360 04	0 360 12
500	400	456	356	15.2	425	325	0 360 55	0 360 09	0 360 15
600	400	556	356	18.7	525	325	0 360 56	0 360 22	0 360 16
700	500	656	456	28.7	625	425	0 360 58	0 360 31	0 360 18
800	600	756	556	40.7	725	525	0 360 59	0 360 33	0 360 19
1000	800	956	756	70.7	925	725	0 360 61	0 360 42	0 360 21
1200		1156		85.7	1125		0 360 64	0 360 46	0 360 87
1400	800	1356	756	100.7	1325	725	0 360 67	0 360 75	0 360 90


■ 11.3 Sectioned uprights and Lina 25 rails to create a frame

Lina 25 sectioned uprights

Réf. 0 361 50/51/52/53/54/55/56




Réf. 0 361 58/59



Sectioned uprights to be cut

Réf. 0 361 92



(1) Prescribed sawing line for upright height step of 25.

The other two provide the height of uprights



Cat. Nos. 0 361 50/51/52/53/54/55/56.

Cabinets height (mm)	Upright length (mm)	Upright Cat. No. (set of 2)
300	237	0 361 50
400	337	0 361 51
500	437	0 361 52
600	537	0 361 53
700	637	0 361 54
800	737	0 361 55
1000	937	0 361 56
1200	1137	0 361 58
1400	1337	0 361 59
Upright to be cut, length 3 m		0 361 92


11. EQUIPEMENTS (CONTINUED)

■ 11.4 Rails


Cat. No. 0 374 02

Cat. Nos. 0 367 80/81/82/83/84/85/86
0 374 07

Cat. No. 0 477 22



Cat. No. 0 477 23




Cabinet width (mm)	Rail length (mm)	Rail Cat. No. 
300	243	0 367 80
400	343	0 367 81
500	443	0 367 82
600	543	0 367 83
800	743	0 367 84
1000	943	0 367 85
1200	1143	0 367 86

2m rail to be cut

Cat. No. 0 374 02 asymmetrical  to the EN 60715 standardCat. No. 0 374 07 symmetrical  depth 15 mmCat. No. 0 477 22 symmetrical  depth 7.5 mm with oblong slotsCat. No. 0 477 23 symmetrical  depth 15 mm with oblong slots


Frame assemblies with Lina 25 rails and uprights



Frame assemblies with Lina 25 rails and uprights (continued)

Envelope dimensions (mm)		Height of uprights	Rail length	Frame mounting	
Height	Width			B	C
400	300	337	243	325	225
500	400	437	343	425	325
600	400	537	343	525	325
700	500	637	443	625	425
800	600	737	543	725	525
1000	800	937	743	925	725
1200		1137		1125	725
1400	800	1337	743	1325	725

■ 11.5 RAL 7035 internal doors



Mounted using Cat. No. 0 363 69.

IP xxB.

Glass fibre-filled polyester, thickness: 4 mm.

Self-extinguishing at 960°C according to the IEC EN 60695-2-11 standard.

Grid integrated into the rear panel.

Centre marked on front panel.

Distance between cabinet door and adjustable internal door: 44 to 52 mm - 5 mm for glass door.

Left or right opening with built-in grip.

Captive hinge pins.

Double bar lock: 1 lock for height 400 to 600 mm, 2 locks from 700 mm height.


Compatible with key cylinders and other imprints.

Cabinets H x L	Dim. (mm) Height x width	Effective dim. (mm) Height x width.	Inner door Cat. No.
400 x 300	341 x 236	305 x 185	0 363 59
500 x 400	441 x 336	405 x 250	0 363 60
600 x 400	541 x 336	505 x 250	0 363 61
700 x 500	642 x 436	500 x 340	0 363 62
800 x 600	742 x 536	600 x 440	0 363 63
1000 x 800	942 x 736	800 x 640	0 363 64
1200 x 800	942 x 736	800 x 640	0 363 65 ⁽¹⁾

⁽¹⁾Door identical to Cat. No. 0 363 64 with 200 mm upper or lower reservation

11. EQUIPMENT (CONTINUED)**11.6.1 Ready-to-use chassis with insulating faceplates in rows
RAL 7035**


In Atlantic stainless steel cabinets, the chassis are mounted on the side studs.



Cabinet	Chassis	
H x W x D (mm)	Cat. No.	Capacity
400 x 300 x 200	4 330 00	3 rows of 10 modules
500 x 400 x 200/250	4 330 01	3 rows of 16 modules
600 x 400 x 200/250	4 330 02	3 rows of 16 modules
700 x 500 x 250/300	4 330 04	4 rows of 21 modules
800 x 600 x 250/300/400	4 330 05	5 rows of 27 modules

**11.6.2 Ready-to-use chassis with monobloc metal faceplate
RAL 7035**


In Atlantic steel cabinets, the chassis are mounted on the front (hinge mounts)







Cabinet	Chassis	
H x W x D (mm)	Cat. No.	Capacity
400 x 300 x 200	4 330 10	3 rows of 10 modules
500 x 400 x 200/250	4 330 11	3 rows of 16 modules
600 x 400 x 200/250	4 330 12	3 rows of 16 modules
700 x 500 x 250/300	4 330 14	4 rows of 21 modules
800 x 600 x 250/300/400	4 330 15	5 rows of 27 modules

**11.6.3 Chassis for customer assembly with insulating faceplates
RAL 7035**

The functional uprights of the chassis can be mounted inside the cabinet at the back, on the universal brackets, or on the depth adjustment kit (0 367 43/44/45).




Cabinet	Chassis		
H x W x D (mm)	Cat. No.	Capacity	Example with 150 faceplate
700 x 500	4 330 20	usable faceplate height 600	4
800 x 600	4 330 21	usable faceplate height 750	5
1000 x 800	4 330 24	usable faceplate height 900	6
1200 x 800	4 330 25	usable faceplate height 1050	7

(mm)	700 x 500	800 x 600	1000 x 800	1200 x 800
	4 330 20	4 330 21	4 330 24	4 330 25
	4 330 50	4 330 51	4 330 52	4 330 52
	4 330 53	4 330 54	4 330 55	4 330 55
	4 330 60	4 330 61	4 330 62	4 330 62
	4 330 63	4 330 64	4 330 65	4 330 65
Module per row	19	25	36	36

11. EQUIPMENT (CONTINUED)

11.6.4 Chassis for customer assembly with metal faceplates
RAL 7035

The functional uprights of the chassis can be mounted inside the cabinet at the back, on the universal brackets, or on the depth adjustment kit (0 367 43/44/45).




Cabinet	Chassis		
H x W x D (mm)	Cat. No.	Capacity	Example with 150 faceplate
700 x 500	4 330 30	usable faceplate height 600	4 + 1 faceplate h50
800 x 600	4 330 31	usable faceplate height 750	5
1000 x 800	4 330 34	usable faceplate height 950	6 + 1 faceplate h50
1200 x 800	4 330 35	usable faceplate height 1150	7 + 2 faceplate h50

(mm)	700 x 500	800 x 600	1000 x 800	1200 x 800
	4 330 30	4 330 31	4 330 34	4 330 35
	4 330 70	4 330 71	4 330 72	4 330 72
	4 330 73	4 330 74	4 330 75	4 330 75
	4 330 76	4 330 77	4 330 78	4 330 78
	4 330 80	4 330 81	4 330 82	4 330 82
	4 330 83	4 330 84	4 330 85	4 330 85
	4 330 90	4 330 91	4 330 92	4 330 92
	4 330 93	4 330 94	4 330 95	4 330 95
Module per row	19	25	36	36

11.6.5 Mounting plate for customer assembly chassis

- Cat. No. 433044 , for width 600
- Cat. No. 433045 , for width 800



They allow you to install power devices on the chassis: the plate references must be completed with a faceplate references of height 300.


- Power distribution block 0 374 00
- Power distribution block 0 374 47
- Vistop
- DRX
- DPX³ 160/250A
- DPX³ 160/250 A with earth leakage module
- DPX IS

11. EQUIPMENT (CONTINUED)

11.6.6 Kit with 2 mounting brackets for customer assembly chassis (4 330 99)

- Bracket kit to adjust the depth of the chassis to be able to mount:
- input or output terminal blocks
 - mounting plates (order 2 kits)

A kit consists of 4 brackets with fasteners.




■ 11.7 Châssis VDI

Used to integrate 19" VDI equipment into 800 mm wide, 300 mm deep stainless steel Atlantic cabinets.

For 400 mm wide cabinets, the chassis accepts the integration of VDI equipment from the XL VDI mini cabinet.


Can be secured directly to the wall for a wall-mounted chassis (without cabinet).



Cat. No.	A (mm)	B (mm)
0 462 28	725	525
0 462 29	725	725

11. EQUIPMENT (CONTINUED)

■ 11.7 VDI chassis (continued)



Atlantic cabinets					
Chassis Cat. No.	Capacity	Cat. Nos	Dimensions	Effective dimensions under door	
				A (mm)	B (mm)
0 462 28	12 U	0 352 05	600 x 400 x 250	145	105
0 462 29	16 U	0 352 11	800 x 600 x 300	145	155

■ 11.8 Cabinet mounting

Directly to the wall or using mounting lugs.



304 L stainless steel plate.

Rated loading: 300 kg per cabinet.

Can be used for horizontal or vertical mounting.




Cat. No. 0 364 06



Cat. Nos.	Vertical lugs		Horizontal lugs		V	Y	E	F
	R	S	T	U				
0 352 00	350	150	250	250	392	292	225	169
0 352 01	450	250	350	350	492	392	325	269
0 352 02	550	350	450	450	592	492	425	369
0 352 03	650	350	550	450	692	492	525	369
0 352 05	650		550		692		525	
0 352 06	750	450	650	550	792	592	625	469
0 352 08	450	550	350	650	492	692	325	569
0 352 11	850		750		892		725	
0 352 13	1050	750	950	850	1092	892	925	769
0 352 14	1250		1150		1292		1125	
0 352 15	1450		1350		1492		1325	

12. ACCESSORIES

■ 12.1 Hinged glass doors



IP 54

Anodised aluminium frame, opening to 120°.


Polycarbonate window, thickness 3 mm. Neoprene seal.

455 key lock.

Supplied with drilling template.

Protect devices, avoid unintentional operations and allow devices to be viewed from the front.


Cat. No.	Outside dimensions (mm)			Window dimensions (mm)		Effective depth (mm)
	Haut.	Larg.	Prof.	Haut.	Larg.	
0 475 45	300	400	50	230	330	42
0 475 46	400	400	50	330	330	42
0 475 47	500	500	50	430	430	42
0 475 48	600	400	50	530	330	42
0 475 49	600	600	50	530	530	42



Cat. No.	Dimensions (mm)			
	A	B	D	E
0 475 45	300	400	230	330
0 475 46	400	400	330	330
0 475 47	500	500	430	430
0 475 48	600	400	530	330
0 475 49	600	600	530	530


■ 12.2 Self-adhesive plastic document holders

- **Cat. No. 0 365 80**, 340 x 235 mm (inside dimensions: 310 x 200 x 18 mm) and Cat. No. 0 365 81, 260 x 165 mm (inside dimensions: 230 x 130 x 18 mm).



■ 12.2 Self-adhesive plastic document holders (continued)

- **Cat. No. 0 365 82**, 325 x 120 mm (inside dimensions: 324 x 120 x 18 mm). IP 50 closure RAL 9002. Capacity: approximately fifteen A4 sheets folded in half.



- **Cat. No. 0 097 99**, 305 x 220 mm (format A4) Transparent, flexible.

■ 12.3 Contact de porte


Cat. No. 0 363 13

3 A - 250 V

1 contact NF - 1 contact NO

For example, can shut off the air conditioning and power the lights when the door is opened.

Supplied with mounting lugs.



■ 12.4 Lighting kit

Cat. No. 0 363 12

Supplied with 8 W fluorescent tube - Ø 16 mm - 230 V - 50 Hz

Class I - IP 20

Shielded in accordance with EN 50015

Equipped with a switch

Connection by strip

Dimensions: 350 x 61 37 mm

■ 12.5 Protective conductor lug

Cat. No. 0 367 36

Set of two support brackets for copper bar or rail for terminal block.

