




Mosaic™ **Controls 10 AX and 20 AX**

Cat. No(s): 0 770 50L/60L/63L/92L







0 770 50L

0 770 60L 0 770 63L

1. USE


General lighting control mechanisms with or without signalling components (indicator light).


The mechanisms can be flush-mounted or surface-mounted. To be equipped with plate.

2. RANGE

| Description | Cat. No |
|--|-----------|
| TWO POLE SWITCH 10 AX - 2 modules To be equipped with an indicator Cat. No 6 650 90 or 6 650 91 for indicator or illuminated function | 0 770 50L |
| TWO POLE SWITCH 20 AX - 2 modules To be equipped with an indicator Cat. No 0 676 64 for indicator or illuminated function | 0 770 63L |
| TWO WAY SWITCH 20 AX - 1 module To be equipped with an indicator Cat. No 0 676 64 for indicator function | 0 770 60L |
| TWO WAY SWITCH 20 AX - 2 modules To be equipped with an indicator Cat. No 0 676 64 or indicator or illuminated function | 0 770 92L |

3. DIMENSIONS (mm)





| Cat. No | Α | В | С | D |
|-----------|----|------|------|------|
| 0 770 50L | 45 | 45 | 31 | 12 |
| 0 770 60L | 45 | 22.5 | 30 | 12.5 |
| 0 770 63L | 45 | 45 | 31.5 | 12.5 |
| 0 770 92L | 45 | 45 | 31.5 | 12.5 |

4. CONNECTION


Type of terminals: with screws Terminal capacity: 2 x 4 mm² Stripping length: 10 mm

Screwdriver: Flat 4 mm - Posidrive n° 1 - Philips n° 1


5. WIRING

■ 5.1 Illuminated function: illuminates the switch in the dark.


0 770 50L



0 770 60L/92L*



0 770 63L*




^{*}Illuminated function mounting not advised with this type of indicator

The indicator light's energy consumption should be taken into account.


5. WIRING (continued)

■ 5.2 Indicator function:


0 770 50L



0 770 60L/92L*



0 770 63L*



*Illuminated function mounting not advised with this type of indicator light.

The indicator light's energy consumption should be taken into account.

6. TECHNICAL CHARACTÉRISTICS

■ 6.1 Mechanical characteristics

Impact tests: IK 04

Protection against solid bodies and liquids: IP 31 D **Nota**: Switching mechanism (handling force 2 to 3 N).

■ 6.2 Material characteristics

Rocker: White RAL 9003 ABS + PC white opalescent

Base: PC

Rocker support: PC

Halogen-free

UV-resistant

Self-extinguishing:

 $850^{\circ}\text{C}/30 \text{ s}$ for insulating components holding live parts in place. $650^{\circ}\text{C}/30 \text{ s}$ for other insulating components.

■ 6.3 Electrical characteristics

Voltage: 250 VAC Current: 20 AX

10 AX for Cat. No 0 770 50L

Max. power for self-ballasted lamps: 100 W for 10 AX 250 W for 20 AX

■ 6.4 Climate characteristics

Storage temperature: - 10° C to + 70° C Usage temperature: - 5° C to + 35° C

7. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

■ 7.1 Resistance to cleaning products

Hexane (EN 60669-1), methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

■ 7.2 Resistance to hospital-type cleaning agents

Anios, Surfanios, Bactilysine, Diluted hydrogen peroxide (35%).

Caution: Always test before using other special cleaning products.

8. ACCESSORIES

Lights for switches with indicator light:

Cat. No 0 676 64 (230 V - 2.4 mA)

Cat. No 6 650 90 (230 V - 0.15 mA

Cat. No 6 650 91 (230 V - 3 mA)

9. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue.