



Céliane™ German standard socket outlets


Cat. No(s): 0 671 45/52/53/61



0 671 53



0 671 52/61



0 671 45


1. USE

Socket outlets 16 A - 250 V.
Mécanismes with lateral cables output.

2. RANGE

Description	References
2 P+E socket with eclips	0 671 53
2 P+E socket with screw cover plate not supplied on mechanism	0 671 52
2 P+E socket with clip cover plate not supplied on mechanism	0 671 61
2 P+E socket with dedicated cover plate supplied on mechanism	0 671 45

3. OVERALL DIMENSIONS (mm)



References	A	B	C	D
0 671 45	45	45	31.7	8.4
0 671 53	45	45	34.6	5.4
0 671 52/61	45	45	31	5.4

4. CONNECTION

■ Cat. No. 0 671 53

Terminal type: automatic
Terminal capacity: 2 x 2.5 mm²
Stripping length: 12 mm

■ Cat. Nos. 0 671 52/61 - 0 671 45

Terminal type: with screws
Terminal capacity: 2 x 2.5 mm²
Stripping length: 10 mm
Screwdriver: Posidrive No 1, Philips No 1, flat-blade 4 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

- Impact tests: IK 04
- Protection against solide/bodies liquids: IP 20

■ 5.2 Material characteristics

- Mechanism: Polycarbonate
- Cover plate: Polycarbonate - Halogen free
- Self-extinguishing:
+ 850°C / 30 s for insulating components holding in place live parts.
+ 650°C / 30 s for the other insulating components.

■ 5.3 Electrical characteristics

Voltage: 250 V~
Current: 16 A

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C
Usage temperature: - 5° C to + 50° C

6. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e-catalogue.