


87045 LIMOGES Cedex

Cat. No(s): 5724 52

Telephone: (+33) 05 55 06 87 87 - Fax: (+33) 05 55 06 88 88

Arteor™

Indicator unit light



1. USE

Signalling indicator lights using different voltage LEDs.


2. RANGE


Designation	Cat. No.	No. of modules	Fixing method	Connection method	Weight (g)
Signalling indicator light with LED	5724 52	1	With clips	With screws	17.9

3. PREPARATION

The mechanisms can be flush-mounted or surface-mounted.


4. OVERALL DIMENTIONS





5. CONNECTION

Type of screwdriver: flat-blade screwdriver 3.5 mm. Terminal capacity: $1 \times 2.5 \text{ mm}^2$ or $2 \times 1.5 \text{ mm}^2$ Stripping length: 8 mm



6. TECHNICAL CHARACTERISTICS

6.1 Mechanical characteristics

Impact tests: IK 04

Protection by solid bodies / liquids: IP 41

6.2 Material characteristics

Base: Polycarbonate

Cover: Polycarbonate (RAL 9003)

6.3 Electrical characteristics

Self-extinguishing: 650°C / 30s

Voltage: 230 V Frequency: 50/60 Hz Power: 1 W

6.4 Climatic characteristics

Storage temperatures: - 10°C to + 70°C Operating temperatures: - 5°C to + 50°C

7. CLEANING

Surface cleaning with a cloth

Do not use: acetone, tar remover, trichloroethylène

7.1 Resistance to cleaning agents

Resistance to the following agents: Hexane (EN-60669-1), Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes

7.2 Resistance to hospital-type cleaning agents

Resistance to the following agents: Anios, Surfanios, Bactilysine, Diluted hydrogen peroxide.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used

8. ACCESSORIES

Delivered with colors filters.

Technical sheet: F00727EN/00 Updated: Created: 02/12/2008