


Céliane™ 10 AX 2-pole switch Cat. No.: 0 670 20




#### 1. USE

Lighting control mechanism. Horizontal and vertical multi-gang mounting. Can be equipped with the full range of Céliane finishes.

#### 2. RANGE

Description	Cat. No.
2-pole switch For simultaneous breaking of phase and neutral. Can be illuminated (with bulb Cat. No. 6 650 90) or signalling (with bulb Cat. No. 6 650 91); takes cover plates (Cat. No. 0 680 21/23 White, Cat. No. 0 683 21/23 Titanium. Cat. No. 0 679 21/23 Graphite).	0 670 20

#### 3. DIMENSIONS (mm)



Cat. No.	Α	В	С	D
0 670 20	45	45	39.5	8.5


## 4. CONNECTION

Terminal type: with screws Terminal capacity: 2 x 4 mm<sup>2</sup> Stripping length: 10 mm


Screwdriver: Posidrive No. 1 - Philips No. 1 - Flat 4 mm

### 5. WIRING

Illumination function: ensures the switch is visible in the dark



Signalling function: state of a circuit



### **6. TECHNICAL CHARACTERISTICS**

#### ■ 6.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid bodies and liquids: IP 31 D

#### ■ 6.2 Material characteristics

Mechanism housing: Polycarbonate

Halogen-free

Self-extinguishing:

 $850^{\circ}\text{C/30}$  s for insulating components holding live parts in place.  $650^{\circ}\text{C/30}$  s for other insulating components.

## ■ 6.3 Electrical characteristics

Voltage: 250 V~ Current: 10 AX

Max. power for self-ballasted lamps: 100 W

# ■ 6.4 Climate characteristics

Storage temperature: -  $10^{\circ}$ C to +  $70^{\circ}$ C Usage temperature: -  $5^{\circ}$ C to +  $50^{\circ}$ C

## 7. ACCESSORIES

Illuminated indicator Cat. No. 6 650 90 (230 V - 0.15 mA) Signalling indicator Cat. No. 6 650 91 (230 V - 3 mA)

## 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.