



Céliane™
6 A push-buttons

Cat. Nos: 0 670 31/31E/34/11/38



0 670 31/31E/34



0 670 11


1. USE

General lighting control mechanisms with or without indicating components.

2. RANGE

Description	Cat. No.
2-way push-button - NO-NC contact 1-gang	0 670 31 0 670 31E
Pushbutton - NO contact 2 volt-free terminals for illuminated function 1-gang	0 670 34
Pull-cord push-button with cord 1.50 m 1-gang	0 670 11
Pull-cord push-button 1-gang	0 670 38

3. DIMENSIONS (mm)




Cat. Nos	A	B	C	D
0 670 31/31E/34	45	45	24	8
0 670 11	45	45	27.5	18.5
0 670 38	45	45	22.5	17.5


4. CONNECTION

Terminal type: automatic
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 12 mm


Cat. No. 0 670 31/31E



Cat. No. 0 670 34



Cat. No. 0 670 11/38





5. WIRING

■ **5.1 Locator function:** ensures the switch is visible in the dark.

Cat. No: 0 670 31/31E

Insert lamp Cat. No. 0 676 86

Use a special cover plate Cat. No. 0 680 03 or 0 683 03 or 0 679 03





■ **5.2 Indicator function (state of a circuit)**

Cat. No: 0 670 34

Insert lamp Cat. No. 0 676 88 (230 Vac).

Use a special cover plate Cat. No. 0 680 03 or 0 683 03 or 0 679 03




5. WIRING (continued)

■ **5.3 Locator function or indicator function with opalescent ring**


Separate lamp

Cat. No. 0 676 70 (230 Vac)



2-wire connection

Cat. No. 0 676 70 (230 Vac)



Special opalescent ring (not supplied)

Break the tabs

Selector indicator (3 mA) or locator function (0.15 mA)

6. TECHNICAL CHARACTERISTICS

■ **6.1 Mechanical characteristics**

Impact tests: IK 04

Penetration by solid bodies and liquids: IP 20

■ **6.2 Material characteristics**

Mechanism: PC

Colour: grey

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place

650°C/30 s for other insulating components

■ **6.3 Electrical characteristics**

Voltage: 250 V~

Current: 6 A

■ **6.4 Climate characteristics**

Storage temperature: - 10°C to + 70°C

Operating temperature: - 5°C to + 35°C

7. ACCESSORIES

Bulbs for switches with indicator:

Locator	Indicator	Locator/Indicator
0 676 86 (230 V/0.15 mA)	0 676 88 distributed phase (230 V/3 mA)	0 676 70 (230 V)
0 676 87 (12/24/48 V)		

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.