


Céliane™ Key switch

Cat. No(s): 0 670 09/39



0 670 09

1. USE


Control mechanism for opening and closing circuits that requires the use of a key.


To be equipped with a barrel Cat. No. 0 697 95 or with a standard european barrel.

2. RANGE

Description	References
2-position key switch - 2 contacts NO Removing the key in the OFF position without modifying the state of the contacts	0 670 09
3-position key pushbutton - Reverser with stop position Removing the key in the OFF position	0 670 39

3. DIMENSIONS (mm)





Α	В	С	D
45	45	52	5.5

4. CONNECTION

Terminal type: with screws Terminal capacity: 2 x 2.5 mm² Compatible flexible or rigid cables Stripping length: 9 mm Screwdriver: Philips No 1

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid and bodies liquids: IP 41 Protection against impact: IK 04

■ 5.2 Material characteristics

Base and cover plate: PC

Self-extinguishing:

- $+850^{\circ}$ C / 30 s for insulating parts holding live parts in place
- $+650^{\circ}$ C / 30 s for the other insulating components

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 10 A Frequency: 50/60 Hz

Max. power capacity: 750 W - 230 V~

48 V== - 3 A

■ 5.4 Climactic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 40° C

6. ACCESSORIES

European barrel Cat. No. 0 697 95 delivered with a single set of 3 keys.

7. STANDADS ANS APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.