
Llegrand[®]

87045 LIMOGES Cedex Telephone: +33 (0)5 55 06 87 87 - Fax: +33 (0)5 55 06 88 88

Céliane™

Loud-speaker socket

Cat. No(s): 673 11



673 11


1. USE


For connecting a loud-speaker.

2. RANGE


Description	Cat. No.	Weight (g)
Loud-speaker socket	673 11	13.5

3. OVERALL DIMENSIONS





4. FITTING



4. FITTING (cont'd)

1 - The mechanism is clipped to the support from the front.

2 - The mechanism/support assembly is screwed to the flush-mounting box.


3 - The cover plate (rocker + ring) is clipped to the mechanism.

4 - The plate is clipped to the support.

Can be fitted with the full range of Céliane finishes.

Vertical or horizontal multi-gang mounting.

This product can be dual-mounted once the side tabs have been broken off.




Céliane™ Loud-speaker socket


5. CONNECTION

Stripping

Recommended cable: Audio cable 2 x 6 mm² max. a - Cable unsheathing length: 30 mm

b - Core stripping length: 6 mm.






b the second sec

Wiring

Terminal type: screw connection Tool: flat-blade screwdriver 0.4 x 2.5 mm Follow the wiring diagram below:



6. TECHNICAL DATA

6.1 Mechanical characteristics Impact tests: IK 04

Penetration by solid/liquid bodies: IP41 (C15-100)

6.2 Material characteristics Base: Polycarbonate Self-extinguishing: 650°C / 30 s

6.3 Climatic characteristics

Storage temperatures: -10°C to +70°C. Operating temperatures: -5°C to +55°C

7. CLEANING

No cleaning

no rocker

Created: 01/09/2008