

87045 LIMOGES Cedex

Telephone: (+33) 05 55 06 87 87 - Fax: (+33) 05 55 06 88 88

Digital detector - Dual Tech

Catalogue number(s): 0 488 22



CONTENTS	Page
1. Use	1
2. Technical features	1
3. Overall dimensions	1
4. Connection	2
5. Installation	2
6. Disassembly	2
7. Settings	3
8. Performance	4
9. Configuration	4
10. Maintenance	5
11. Standards	5

1. USE

This device allows a light source to be controlled automatically via a controller through the detection of movement in its surveillance zone.

Movement detector with detection angle of 360°. Detection type: infra-red (PIR) and ultrasound (US)

Assembly type: ceiling

2. TECHNICAL FEATURES

Voltage: 27 V=

No load power consumption: 17 mA

Connection between detector and actuator: RJ 45 lead or cable or

BUS/SCS cable to be fitted with RJ 45 connector


Flush-mounting diameter: 65 mm without flush-mounting box, 68 mm with flush-mounting box

Weight: 150 g


Impact resistance: IK04


Penetration by solid and liquid matter: IP20 Usage temperature: -5°C to +45°C Storage temperature: -20°C to +70°C

Cover removed



3. OVERALL DIMENSIONS





Technical data sheet: F01127EN/02 Updated on: 24/11/2017 Created on: 18/05/2010


CONTENTS 1/5

Catalogue number(s): 0 488 22


4. CONNECTION

Type of terminals: RJ 45







RJ 45 patch and equipment cords




RJ 45 - BUS/SCS connector




RJ 45 doubler



Option: It is possible to manage the detector by infra-red remote control.







Technical data sheet: F01127EN/02

Updated on: 24/11/2017

Catalogue number(s): 0 488 22

7. SETTINGS

- Parameters:

Detection parameters		Default value	Modifiable parameters	Configuration tools	
				88230	88235
Time	delay	15 mins	3,5,10,15,20 mins	-	✓
Tille	delay	13 1111115	30s - 255 h 59 min 59s	✓	-
		US (high)	Law madium high yang		
Sensi	itivity	PIR (very high)	Low, medium, high, very high	✓	✓
Davli	ght setpoint	500 lux	20, 100, 300, 500, 1000 lux	-	✓
			0 - 1275 lux	✓	-
	Auto on/Auto off	Inactive	Enabled/Disabled	✓	✓
des	Walkthrough	Active	Enabled/Disabled	✓	✓
Modes	Manual on/Auto off	Inactive	Enabled/Disabled	✓	✓
	Partial on/Group off	Inactive	Enabled/Disabled	✓	-
5 0	Initial	PIR and US	PIR and/or US, PIR, US	✓	-
Detection scheme	Maintain	PIR or US	PIR and/or US, PIR, US	✓	-
S S	Retrigger	PIR or US	PIR and/or US, PIR, US, Disabled	✓	-
Alert		Inactive	Enabled/Disabled	✓	
Advanced mode	Calibration	-	0 - 99995 lux	✓	-
	Light regulation	Inactive	Enabled/Disabled	✓	-
	Provision of light	Auto	Auto - 1275 lux	√	
Ad	Loop type	Close loop	Open - Close	✓	-

Time delay: Length of time the load is on after a detection is made.

Sensitivity: Detection range setting.

Daylight setpoint: Value at which the load comes on if light is less than the setting and goes off if it is above this threshold.

Auto on/Auto off mode:

Comes on automatically:

- At the detection of a presence if there is an insufficient natural level of light. Turns off automatically:
- If no presence is detected and at the end of the time delay set.
- Or if there is a sufficient natural level of light (activated setting)

Any new detection causes an automatic switch on if there is insufficient light.

Walkthrough:

- If there is no presence detected in the 3 minutes following an initial detection, the product will cut off after 3 minutes.
- If a new presence is detected in the 3 minutes following the initial detection, the device will cut off at the end of the time delay set.

Manual on/Auto off mode:

Comes on via a manual switch, automatic switch off:

- Where no presence is detected and at the end of the time delay set.

Following switch-off any new detection within a 30 second period will cause the device to be switched on automatically.

After 30 seconds the device is switched on via a manual switch.

7. SETTINGS (continued)

Partial on/Group off mode:

Possibility of controlling one or more lighting points individually.

In this mode it is essential for a lighting group to be created:

- Either by manual teach phase.
- Or from the advanced configuration tool cat. no. 882 30 by using the function "PnL capteur" (PnL detector).

The detector switches the loads on that are linked to it via the actuator. Where there is no detection and at the end of the time delay it switches off all loads in the group to which it belongs.

Initial detection: The load is switched on with the first detection made.

Maintain: The load remains active if any new presence is detected

Retrigger: Function allowing automatic start of the product at the end of 30 seconds following the load being switched off.

On being switched off any new detection within a 30 second period will cause the device to be switched on automatically.

After 30 seconds the device must be switched on manually.

Rating: The surrounding level of light measured with a luxmeter will then have to be transmitted to the detector.

Light regulation: Automatic switch-off of the load 10 minutes after the Daylight setpoint is exceeded. If the level of light is less than the Daylight setpoint, the load is activated automatically after 20 seconds.

Provision of light: Quantity of additional lux brought in by the load being switched on.

 $\mbox{\bf Loop type:}$ -Close loop: the sensor reads the value of it's own lighting cell for light measurement.

-Open loop: the sensor reads the value of an external lighting cell for light measurement.

- Modification of the parameters by the configuration tools



- 882 35: Simplified configuration tool
- 882 30: Advanced configuration tool

When the detector receives an PIR command using the configuration tool it emits a beep acknowledging the modification.

- Return to factory settings:

1st press: Where LEARN is pressed for a short period the LED flashes slowly.

2nd press: Keep LEARN pressed down for 10 seconds until the LED flashes quickly.


Technical data sheet: F01127EN/02 Updated on: 24/11/2017 Created on: 18/05/2010


CONTENTS 3/5

Catalogue number(s): 0 488 22

8. PERFORMANCE

Height





- PIR Detection

		Sensitivity Low (25%)		Sensitivity Medium (50%)	
		Ø (m)	Surface (m²)	Ø (m) Surface (n	
Height (m)	2.5	4	15	6	25
	3	5.5	25	6.5	35
	4	6.5	35	7.5	45
	5	6	30	10.5	90
	6	4	15	5.5	25

		Sensitivity High (75%)		Sensitivity Very high (100%)	
		Ø (m) Surface (m²)		Ø (m) Surface (m	
Height (m)	2.5	6.5	30	8	50
	3	8.5	60	11.5	100
	4	12.5	125	14	155
	5	12	115	16.5	215
	6	8.5	60	12.5	125

- US Detection

		Sensitivity Low (25%)		Sensitivity Medium (50%)	
		Ø (m) Surface (m²)		Ø (m)	Surface (m²)
	2.5	4	15	4	15
Height (m)	3	6	30	6	30
	4	6	30	6	30
	5	6	30	6	30
	6	0	0	6	30

		Sensitivity High (75%)		Sensitivity Very high (100%)	
		Ø (m) Surface (m²)		Ø (m)	Surface (m²)
Height (m)	2.5	6	30	11	95
	3	8	50	13	150
	4	10	80	13	150
	5	10	80	13	130
	6	10	80	13	130

9. CONFIGURATION (MYHOME_Suite solfware)

Module enabling		Yes - No			
Function type		Stand alone presence sensor Scenarios daylight and presence sensor Scenarios daylight sensor Scenarios presence sensor Stand alone daylight sensor Stand alone daylight and presence sensor			
	o point	Area	0 - 10		
	Point to point	Light point	0 - 15		
type		Group number	0 - 255		
sing		Referent area address	0 - 10	1 address of the group	
Adressing type	۵	Referent light point add	0 - 15	1 address of the group	
¥	Group	Enable secondary group	Yes - No)	
	0	Group sensor 1	0 - 255		
		Group sensor 2	0 - 255		
		Enable load control	Enabled	d - Disabled	
O	oera	ting mode			
PI	R sei	nsitivity			
US	ser	nsitivity			
_In	itial	detection			
	Maintain detection				
	Retrigger		See Chapter 7 SETTINGS (Parameters)		
_	Alert				
_	Loop type				
	Daylight setpoint (lux)				
	Provision of light (lux)				
Lig	Lighting regulation				

Stand alone presence sensor: the sensor send «ON» command to its associated load or group of load according to presence delection.

Stand alone daylight sensor: the sensor send «ON» command to its associated load or group of load according to light parameters.

Stand alone daylight and presence sensor: the sensor send «ON» command to its associated load or group of load according to presence delection and light parameters.

Scenarios presence sensor: the sensor send «CEN» command to the MH202 (scenario programmer) according to presence detection.

Scenarios daylight sensor: the sensor send «CEN» command to the MH202 (scenario programmer) according to light parameters.

Scenarios daylight and presence sensor: the sensor send «CEN» command to the MH202 (scenario programmer) according to presence detection and ight parameters.

Enable secondary group: Activate a group managed by another sensor.

Enable load control: Manage/Don't manage its associated group of loads.



Catalogue number(s): 0 488 22

10. MAINTENANCE

Keep the lens clean.

Clean the surface with a cloth.

Do not use: acetone, tar-removing cleaning agents or trichloroethylene.

Maintenance with the following products: - Hexane (En 60669-1),

- Methylated spirit,
- Soapy water,
- Diluted ammonia,
- Bleach diluted to 10%,
- Window-cleaning products.

CAUTION: An initial test is required for the use of other special maintenance products.

11. STANDARDS

Directive: CE

Installation standards: NFC 15-100 Product standards: IEC 60669-2-1

Environmental standards:

- EU Directive 2002/96/EC:

WEEE (Waste Electrical and Electronic Equipment)

- EU Directive 2002/95/EC:

RoHS (Restriction of Hazardous Substances)

- Regulations: ERP (public buildings)

ERT (workplace buildings) IGH (high-rise buildings)

Technical data sheet: F01127EN/02 Updated on: 24/11/2017 Created on: 18/05/2010 **Lipinal**

CONTENTS 5/5