


87045 LIMOGES Cedex

Telephone: 33 0 5 55 06 87 87 - Fax: 33 0 5 55 06 88 88

Céliane™

Touch-control switch with no neutral 400 W

Cat. No(s): 670 41




1. USE


For switching lights on or off with only the lightest stroke.

2. RANGE


Description	Cat. No.	Weight (g)
Touch-control switch with no neutral 400 W	670 41	57.6

3. OVERALL DIMENSIONS





4. FITTING



* not supplied with the mechanism

4. FITTING (cont'd)

- 1 The mechanism is clipped to the support from the back.
- $\ensuremath{\mathbf{2}}$ The mechanism/support assembly is screwed to the flush-mounting box
- 3 The rocker is clipped to the mechanism
- 4 The plate is clipped to the support

Can be fitted with the full range of Céliane finishes.

Vertical or horizontal multi-gang mounting.

5. CONNECTION


Number of terminals: 3 Terminal type: with screws

Terminal capacity: 2 x 1.5 mm 2 or 1 x 2.5 mm 2


Tool: flat screwdriver 3.5 mm

or Philips No. 1 or Posidriv No. 1 or mixed size 0 Stripping length: 8 mm

5.1 Connection of lighting point



5.2 Connection combined with one or several mechanical pushbuttons



Céliane™

Touch-control switch with no neutral 400 W

6. TECHNICAL DATA

6.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid/liquid bodies: IP 20

} no rocker

Cat. No(s): 670 41


6.2 Material characteristics

Cover: Polycarbonate Base: Polycarbonate

6.3 Electrical characteristics

Self-extinguishing: 650°C / 30 s

Voltage: 100-240 V Frequency: 50/60 Hz



- 1 Incandescent lamp
- 2 Halogen lamp
- 3 ELV halogen lamp with ferromagnetic transformer
- 4 ELV halogen lamp with electronic transformer

6.4 Climatic characteristics

Technical sheet: F00627EN/00

Storage temperatures: -10°C to +70°C Operating temperatures: -5°C to +50°C

7. CLEANING

No cleaning

Updated: