


# Arteor™ Weatherproof plate

Cat. No(s): 575 190



## 1. USE


Weatherproof Arteor plate for covering a 2-module mechanism.  
Supplied with a frame.

## 2. RANGE

	Designation	Cat. No.	Number of modules	Fixing method	Weight (g)
	Weatherproof plate	575 190	2	with screws	75


## 3. MOUNTING

Flush-mounting only.  
The plate is screwed to the support frame by 4 screws (supplied).



- 1 - Clip the device to the support frame
- 2 - Screw the plate to the support frame
- 3 - Clip the insert to the plate.

## 4. OVERALL DIMENSIONS



## 5. TECHNICAL CHARACTERISTICS

### 5.1 Mechanical characteristics

Impact tests: IK 04  
Protection by solid bodies/liquids: IP 44

### 5.2 Material characteristics

Plate: ABS - SEBS  
Flap cover: PP - SEBS  
Antibacterial treatment based on ceramic loaded with silver stain: lifetime of 5 years.  
Self-extinguishing 650°C / 30 s

### 5.3 Climatic characteristics

Storage temperatures: - 10°C to + 70°C  
Operating temperatures: - 5°C to + 50°C

## 6. CLEANING

Surface cleaning with a cloth.  
Do not use: acetone, tar remover, trichloroethylene.

### 6.1 Resistance to cleaning agents

Resistance to the following cleaning agents: Hexane (EN 60669-1), Methylated spirits, Soapy water, Diluted ammonia, Pure bleach diluted 10%, Glass cleaning substance, Pre-impregnated wipes.

### 6.2 Resistance to hospital-type cleaning agents

Resistance to the following agents: Anios, Surfanios, Bactylsine, Diluted hydrogen peroxide (35%).

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

## 7. SPECIAL USE

Arteor plates must not be painted.