


87045 LIMOGES Cedex France

Tel: + 33 (0) 5 55 06 87 87 - Fax: + 33 (0) 5 55 06 88 88

Catalogue number(s): 4146 25/26/27/28/29/30

Fuses for photovoltaic (PV) and direct current (DC) applications



CONTENTS	PAGES
1. General characteristics	1
2. Dimensions	1
3. Technical characteristics	1- 2

1. GENERAL CHARACTERISTICS

10x38 mm cylindrical fuses for protecting the DC side of photovoltaic (PV) installations and DC lines up to 1000 V DC.


gPV fuses as per IEC 60269-6.


This "Uocstc" voltage (short circuit voltage) must always be greater than the maximum PV generator voltage Uocmax (where Uocmax = k Uocstc) irrespective of the ambient conditions (temperature, sunlight, etc.).

For single crystal or polycrystalline panels, the value of k can be determined using Table 1 in the UTE C 15-712 guide. In the absence of any additional temperature information, the value of k can be taken as equal to $1.2 \times \text{Uocstc}$.

For other solar panel technologies, refer to the manufacturer's recommendations.

2. DIMENSIONS






3. TECHNICAL CHARACTERISTICS

Cat. No.	Nominal rating (A) (rated current In)	Dissipated power (w) at 0.7 In (at 20℃)
4 146 25	5	0.58
4 146 26	8	0.73
4 146 27	10	0.67
4 146 28	12	0.72
4 146 29	15	0.91
4 146 30	20	1.09

Operating voltage (Ue)	1000 V DC
Min. breaking capacity	1.35 ln
Max. short-circuit current (Isc) (max. breaking capacity)	10 kA
Time constant (L/R)	1 ms
Operating temperature	-25℃ +60℃
Storage temperature	-30℃ +70℃
Dimensions (mm)	10 x 38
Туре	DC, gPV

Resistance to low overcurrents: 2 x In (I5: see IEC 60269-6)


Derating Kfactor



Ambient temperature

DC voltage curve

OC voltage (V)




L/R time constant (ms): 1 ms

Conforming to standard IEC60269-1


Fusion curve

Time in seconds



Intensity in Amperes

Time in seconds



Intensity in Amperes

Technical data sheet: FR01249EN/01

Updated: 01/02/2013

Created: 28/03/2012

