



Céliane™ Antibacterial* cover plates


Cat. No(s): 0 677 40/41/42/43/44/45/47/48/49



0 677 40



0 677 44










0 677 46

1. USE




Cover plates for Céliane mechanisms.

These products are made of silver-ion based antimicrobial* material. This technology allows the reduction of several types of bacteria. Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc.) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc.). These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.


2. RANGE

	Designation	White antimicrobial*
	Cover plate for 2-way switch or single push-button (for mechanisms 0 670 01/31)	0 677 40
	Cover plate for double 2-way switch or double push-button (for mechanisms 2 x 0 670 01/31)	0 677 41
	Cover plate for 2-way switch or single push-button with indicator light (for mechanisms 0 670 01/31)	0 677 42
	Cover plate for double 2-way switch or double push-button with indicator light (for mechanisms 2 x 0 670 01/31)	0 677 43
	Cover plate for dimmer switch (for mechanisms 0 670 81/82/84)	0 677 48
	Cover plate for roller shutter control (for mechanisms 0 670 01/02)	0 677 49
	Cover plate for socket outlet franco-belgian standard (for mechanisms 0 671 10/11/13)	0 677 44

2. RANGE (continued)

	Designation	White antimicrobial*
	Cover plate for T-shaped telephone socket (for mechanism 0 673 38)	0 677 45
	Cover plate for Cat. 5 RJ45 socket (for mechanism 0 673 37)	0 677 46
	Cover plate for single TV socket (for mechanisms 0 673 80/82)	0 677 47

3. DIMENSIONS (mm)



Cat. Nos	Ø A	B
0 677 40/41/42/43/48	53	9,6
0 677 44	53	16,8
0 677 45/47	53	7
0 677 46	53	7,7
0 677 49	53	8,9
0 677 50	53	6,5
0 677 60	53	18,8

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Protection against impact: IK 04

Protection against solid/bodies and liquids: IP 20

■ 4.2 Material characteristics

Cover plates: ABS White RAL 9003 + antimicrobial* treatment

Indicator light diffuser (Cat. No 0 677 42/43): PC + antimicrobial* treatment.

Halogen-free

UV-resistant

Self-extinguishing: 650° C/30 s

■ 4.3 Climate characteristics

Storage temperature: - 10°C to + 70°C

Usage temperature: - 5°C to + 35°C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the cleaning agents: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Pure bleach diluted to 10%, Window-cleaning products, Pre-impregnated wipes.

Resistance to type cleaning hospital: Anios, Surfianos, Bactilycine, Diluted hydrogen peroxide (35 %).

Caution: Always test before using other special cleaning products

Do not paint the plates.

6. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.

See e.catalogue.

*Contains silver ions that limit the development of bacteria on the surface.