



Arteor™

Double pole switches with indicator


Cat. no(s): 5 720 14/47/49 - 5 721 86/87/88/89/90/91 - 5 724 51
 5 725 14/47/49 - 5 730 32/33/76/78
 5 731 32/33/48/49/76/78



5 720 14 - 5 721 86/87 - 5 725 14



5 720 49 - 5 721 91 - 5 725 49











5 730 76 - 5 731 48/76

1. USE


Général lighting control mechanisms with signalling elements (indicator light or marking).

2. RANGE


	Designation	Finishes					No. of modules	Connection method	Characteristics
		White	Magnesium	Red	Soft alu	Champagne			
	Double pole switch one way with indicator (square)	5 720 14	5 725 14	-	5 721 86	5 721 87	1	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator (square)	5 720 47	5 725 47	-	5 721 88	5 721 89	2	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator and water heater marking (square)	5 720 49	5 725 49	-	5 721 90	5 721 91	2	with screws	20 AX - 250 VAC
	Double pole switch (square)	-	-	5 724 51	-	-	1	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator (round left)	5 730 32	5 731 32	-	-	-	1	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator (round right)	5 730 33	5 731 33	-	-	-	1	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator (round)	5 730 76	5 731 76	-	5 731 48	-	2	with screws	20 AX - 250 VAC
	Double pole switch one way with indicator and water heater marking (round)	5 730 78	5 731 78	-	5 731 49	-	2	with screws	20 AX - 250 VAC

3. PREPARATION

The mechanisms can be flush-mounted or surface-mounted




4. OVERALL DIMENSIONS



5 720 14 - 5 721 86/87
 5 725 14/51
 5 730 32/33 - 5 731 32/33

5 720 47/49 - 5 721 88/89/90/91
 5 725 47/49
 5 730 76/78 - 5 731 48/49/76/78



5. CONNECTION

Terminals: with screws
 Capacity and stripping:

	Capacity			Stripping
5 720 14 - 5 721 86/87 5 724 51 - 5 725 14 5 730 32/33 - 5 631 32/33	4 x 2.5 mm ²	1 x 4 mm ²	1 x 6 mm ²	8 mm
5 721 88/89/90/91 5 720 47/49 5 725 47/49 - 5 730 76/78 5 731 48/49/76/78	4 x 2.5 mm ²	2 x 4 mm ²	1 x 6 mm ²	10 mm

Screwdriver: 4 mm flat-blade up to 5.5 mm

6. OPERATION

Switching mechanism.

7. TECHNICAL CHARACTERISTICS

■ 7.1 Mechanical characteristics

Impact tests: IK 04

Protection by solid bodies / liquids: IP 40 (mounted)
 IP 20 (alone)

■ 7.2 Material characteristics

Rocker: Polycarbonate

Base: Polycarbonate

Basket: Polypropylene

■ 7.3 Electrical characteristics

Voltage: 250 VAC

Current: 20 AX

Self-extinguishing: 650° C / 30 s.

Red light indicator: LED

■ 7.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C

Operating temperatures: - 5° C to + 50° C

8. CLEANING

Surface cleaning with a cloth

Do not use: acetone, tar remover, trichloroethylene

Resistance to the following cleaning agents: Hexane (EN-60669-1), Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

9. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.

Refer to e-catalogue.

