



Arteor™ Lighting controls 20 AX


Cat. No(s): 5 700 09/10 - 5 710 09/10 - 5 720 09/10/41 - 5 723 80/81
 5 725 09/10/41 - 5 730 20/21/22/23/24/25/70
 5 731 20/21/22/23/24/25/39/40/41/42/43/44/45/70



5 700 09 - 5 710 09
 5 720 09 - 5 725 09



5 720 41 - 5 723 80/81
 5 725 41



5 730 70 - 5 731 42/70


1. USE

Lighting controls mechanisms.
 Mechanisms supplied with rocker plates
 To be equipped with support frames and plates.
 Flush-mounting or surface-mounting.

2. RANGE

Désignation	White	Magnesium	Soft Alu	Champagne
1-way switch (square) - 1 module	5 720 09	5 725 09	5 710 09	5 700 09
1-way switch (round left) - 1 module	5 730 20	5 731 20	5 731 39	-
1-way switch (round middle) - 1 module	5 730 21	5 731 21	5 731 40	-
1-way switch (round right) - 1 module	5 730 22	5 731 22	5 731 41	-
1-way switch (square) - 2 modules	5 720 41	5 725 41	5 723 80	5 723 81
1-way switch (round) - 2 modules	5 730 70	5 731 70	5 731 42	-
2-way switch (square) - 1 module	5 720 10	5 725 10	5 710 10	5 700 10
2-way switch (round left) - 1 module	5 730 23	5 731 23	5 731 43	-
2-way switch (middle) - 1 module	5 730 24	5 731 24	5 731 44	-
2-way switch (round right) - 1 module	5 730 25	5 731 25	5 731 45	-

3. OVERALL DIMENSIONS (mm)



	A	B	C	D
1 module	45	22.5	42	13
2 modules	45	45	42	13

4. CONNECTION

Terminals: with screws
 Capacity: 4 x 2.5 mm² or 2 x 4 mm² or 1 x 6 mm²
 Stripping length: 10 mm
 Screwdriver: 4 mm flat-blade up to 5.5 mm

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20 (alone)
 IP 40 (mounted)
 Protection against impact: IK 04

5.2 Material characteristics

Material: Rocker: PC
 Mechanism casing: PC
 Basket: PP

Halogen-free
 UV-resistant

Self-extinguishing:
 850°C/30 s for insulating parts holding live parts in place
 650°C/30 s for other insulating components

5. TECHNICAL CHARACTERISTICS *(continued)*

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 20 AX

Max. power for self-ballasted lamps: 250 W

Frequency: 50/60Hz

■ 5.4 Climate characteristics

Storage temperature: - 10°C to + 70°C

Usage temperature: - 5°C to + 50°C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to cleaning products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Pure bleach diluted to 10%, Window-cleaning products, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e. catalogue.