


Forix[™] IP 44 Push-buttons

Cat. No.(s): 7 823 64/84



1. USE


General lighting control mechanisms.

Mechanisms with single, large rocker can be illuminated using lamp Cat. No. 7 823 98.

2. RANGE

Finishes		Decignation
White	Grey	Designation
7 823 64	7 823 84	One gang push-button

3. OVERALL DIMENSIONS



4. CONNECTION

Stripping: 10 mm
Terminal type: with screws
Terminal capacity up to: 2 x 2.5 mm²
Recommended screwdriver size: pozidrive No. 2
Recommended tightening torque: 0.5 Nm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against liquids: IP 44 Impact tests: IK 07

■ 5.2 Material characteristics

Box: ABS Rocker: ABS Mechanism: PC Conduit gland: SEBS

■ 5.3 Electrical characteristics

Voltage: 250 VAC Current: 6 A

■ 5.4 Climatic characteristics

Storage and use temperature: - 25° C to + 60° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane (EN 60669-1), Methylated spirits, Soapy water, Diluted ammonia, Diluted pure bleached 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

■ 7.1 Lamps

Become illuminated with lamp Cat. No 7 823 98

■ 7.2 Spare membrane glands

White membrane Cat. No 7 823 79 Grey membrane Cat. No 7 823 99