


Céliane™

Double USB socket - Type-A - 3.0 A

Cat. No(s): 0 674 62 - 0 677 15/16



0 674 62



0 677 15/16


1. USE


For recharging portable devices such as phones, smartphones, tablets MP3 or MP4 players, loudspeakers, watches, game consoles, powerbanks.


2. RANGE


Description	Mechanism	White	Titane
Double USB sockets - 5 V== - 3.0 A	0 674 62	0 677 15	0 677 16

3. OVERALL DIMENSIONS (mm)









	Α	В	С	D	ØE
0 674 62	45	45	40.5	7	-
0 677 15/16	45	45	41.5	8.5	53

4. CONNECTION

Type of terminals: with screws Terminal capacity: 2 x 2.5 mm² Stripping length: 6 mm Screwdriver: flat 3.5 mm

4. CONNECTION

Circuit breaker: 16 A MAXI

Necessary safety precautions:



Switch OFF the power at the main circuit breaker. Make sure that the power is OFF besfore continuing with the installation.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Base: PC classe V-0 Front cover: PC

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of $\pm\,20^\circ$ and after 30 minutes of operation.

Nominal input voltage	100-240 V~		
Nominal input frequency	50/60 Hz		
Nominal output voltage	5.0 V		
Nominal input current	0.3 A		
Maximum output current	3.0 A		
Power consumption	15.0 W		
Average efficiency in active mode	84.43 %		
Stand-by power consumption	< 0.07 W		
Consumption class without load and average level of efficiency: Level VI*			
Protection class	II - Low voltage		

*NB: European Regulation No. 278/2009 of 6 April 2009, Directive 2005/125/EC on eco-design requirements for AC/DC power supplies

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

■ 5.4 Climate characteristics

Storage temperature: - 20° C to + 70° C Usage temperature: 0° C to + 40° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards. Refer to e-catalogue.

Created: 15/11/2012 La legrand