

HD4005M2A

1. USE

Rocker, axial or style control device for lighting and other control.

2. RANGE

AXIAL PUSH-BUTTON

Designation	Terminals			
	Screwless		With screws	
	1 module	2 modules	1 module	2 modules
1 P (NO) 10 A 250 VAC	HD4005A HC4005A HS4005A	HD4005M2A HC4005M2A HS4005M2A	HD4005 HC4005 HS4005	HD4005M2 HC4005/2 HS4005/2

STYLE PUSH-BUTTON

Designation	Terminals with screws	
	1 module	2 modules
1 P (NO) 10 A 250 VAC	HZ4005 HX4005 HY4005	HZ4005M2 HX4005/2 HY4005/2


ROCKER PUSH-BUTTON

Designation	Terminals			
	Screwless		With screws	
	5 module	2 modules	5 module	2 modules
1 P (NO) 10 A 250 VAC	HD4055A HC4055A HS4055A	HD4055M2A HC4055M2A HS4055M2A	HD4055 HC4055 HS4055	HD4055M2 HC4055/2 HS4055/2

Color code:

- White : HD
- Tech : HC
- Anthracite : HS

3. OVERALL DIMENSIONS (mm)



	A	B	C	D
Axial				
1 module	45	22.5	34	9.5
2 modules	45	45	28	9.5
Style				
1 module	45	22.5	34	9.5
2 modules	45	45	28	9.5
Rocker				
1 module	45	22.5	24.5	9.5
2 modules	45	45	24.5	9.5

4. CONNECTION

Stripping length (rigid or flexible cables): 12 mm for screwless terminals
9 mm for screw terminals

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D
Impact test: IK 04

■ 5.2 Material characteristics

Material: Polycarbonate for mechanism case
PC for key cover
Colour: White, Tech, Anthracite
Halogen free.
UV resistant.
Self-extinguishing:
- 850° C / 30 s for insulating parts holding live parts in place.
- 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 VAC
Current: 10 A

■ 5.4 Climatic characteristics

Storage and operating temperatures: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichloroethylene.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
Refer to e.catalogue.