


HD4011S







HD4016

1. USE

Switches 32 A and knob selector switch.


2. RANGE

SWITCHES 32 A	Cat. Nos.
 32 A DP switch with led lamp and supporting frame	<input type="checkbox"/> HD4011S <input type="checkbox"/> HC4011S <input type="checkbox"/> HS4011S
 32 A DP switch with led lamp and supporting frame Marked water heater	<input type="checkbox"/> HD4011SW <input type="checkbox"/> HC4011SW <input type="checkbox"/> HS4011SW
SWITCHES 45 A	
 45 A switch with neon and supporting frame (to complete with HA4829... or HB4829... cover plates)	<input type="checkbox"/> HD4019 <input type="checkbox"/> HC4019 <input type="checkbox"/> HS4019
KNOB SELECTOR SWITCH	
 Selector switch - Rotary switch, 1 way - 4 positions for controlling air-conditioners, fans, etc. - 3 A - 250 Vac	<input type="checkbox"/> HD4016 <input type="checkbox"/> HC4016 <input type="checkbox"/> HS4016

Color code:

White Tech Anthracite

3. OVERALL DIMENSIONS (mm)



Rocker	Plate	A	B	C	D
1 module	-	45	22.5	33	13
HD/HC/HS4019	HA4829	95	127	33	14
HD/HC/HS4016	-	45	45	26.5	14

4. CONNECTION

Stripping length (rigid or flexible cables): 12 mm for screwless terminals
9 mm for screw terminals

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D
Impact test: IK 04

■ 5.2 Material characteristics

Material: Polycarbonate for mechanism case
PC for key cover
Colour: White, Tech, Anthracite
Halogen free.
UV resistant.

Self-extinguishing:

- 850° C / 30 s for insulating parts holding live parts in place.
- 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 VAC

■ 5.4 Climatic characteristics

Storage and operating temperatures: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
Refer to e.catalogue.